

## Category 6A Shielded Keystone Socket



### **Contractor Grade Category 6A Shielded Keystone Socket (SGKSbt)**

Our Category 6A contractor grade, die-cast fully shielded socket offers a toolless keystone solution for most shielded Category 5e, Category 6 and Category 6A STP requirements.

#### **Features**

- Compliant with ANSI/TIA 568 C.2 standard – comfortably achieves permanent link level
- Compliant with IEC60512-99-001 – suitable for use with IEEE 802.3at (PoE+) applications
- Quick and easy tool-less lever “butterfly” style termination
- Fully shielded die-cast body is robust as well as offering excellent performance in eliminating alien cross-talk
- Compact housing suitable for use in high density installations e.g. 0.5U panels
- Standard format keystone fits a wide range of panels, adaptors and faceplates
- Suitable for 22-24 AWG both stranded and solid wire. (0.64– 0.51 mm)
- Panel mount and D UNIVERSAL versions also available

### Specifications

- Weight: 24g approx
- Dimensions: 47 x 24 x 18mm approx. (including primary packaging)
- Colour: Silver
- Materials: Zinc alloy housing; 50µ"/1.27µm gold plating over nickel over phosphor bronze on contacts
- Plug insertion life: > 750 insertions
- IDC Terminal Life: > 250 insertions
- Supplied with cable tie
- Operating temperature: -10°C to 60°C

**Packaging:** SGKSbt: Packed in individual polybags then in cartons of 50  
SGKSbt#24: Packed in carton of 24 pcs without individual poly bags

### EAN:

SGKSbt: 5055386512765  
SGKSbt#24: 5055386512772  
SGKSbtBpm: 5055386512789  
SGKSbtDSpm: 5055386512796

**Commodity Code:** 85444920

**Country of Origin:** China

How to wire the SGKSbt video <https://youtu.be/7OtCrcvjxGo>



