

## Product information

# 82 01 150 SB

## KNIPEX TwinGrip

Front and side gripping plier



- Gripping, tightening and loosening screws with worn heads and threads
- Unique combination: Front grip and side grip function, box joint, push button adjustment
- High-grip front jaw with robust teeth and high gear ratio at the tip of the mouth
- Small and handy – also suitable for more delicate work
- Large front and side gripping capacities: for diameters and width across flats 3 – 16 mm
- Very slim pliers: work even in confined spaces, with slim turning zone for fast screwing
- Reliable, frontal gripping of flat workpieces up to 6 mm thanks to three-point system
- Three-way adjustable slip joint with push button adjustment for precise alteration of gripping capacity
- Optimised geometry of the side jaw design: with locking effect for maximum grip when loosening and tightening
- Pinch stop reduces the risk of crushed fingers
- Durable and resilient thanks to robust box joint

### General

Article No.	82 01 150 SB
EAN	4003773091004
pliers	grey atramentized
head	polished
handles	covered with non-slip plastic
Weight	130 g
Dimensions	154 x 85 x 18 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

adjustment positions	3
Capacities for pipes (diameter)	Ø 1/8 – 5/8 Inch
Capacities for pipes (diameter)	Ø 3 – 16 mm
Capacities for nuts	3 – 16 mm
Capacities for nuts	1/8 – 5/8 Inch

*technical change and errors excepted*



