



HDAN6-BL-SW

- hygienic design
- mounting for potentiometer
- with and without end stop

Data

Ordering data

Product type description	HDAN6-BL-SW
Article number (order number)	103041115
EAN (European Article Number)	4030661617183
eCl@ss number, version 12.0	27-37-12-13
eCl@ss number, version 11.0	27-37-12-13
eCl@ss number, version 9.0	27-37-12-13
ETIM number, version 7.0	EC000222
ETIM number, version 6.0	EC000222

Approvals - Standards

Certificates	hygiene tested
--------------	----------------

General data

Standards	EN IEC 60947-5-1 EN IEC 60947-1 DIN EN 1672-2
Versions	Front plate mounting
Design	Round

Toggle	round
Sealing type	Membrane Lip gaskets
Material of the operators	Plastic
Material of the front ring	stainless steel
Colour of the operating element	Black
Colour of the front ring	Silver
Colour of the bellows	Blue
Gross weight	136 g

Mechanical data

Mounting	central nut
Tightening torque of nuts, maximum	4 Nm

Mechanical data - Dimensions

Mounting height	31 mm
Note (Mounting height)	Height in front of the front panel.
Mounting depth	71 mm
Note (Mounting depth)	Depth behind front panel without potentiometer
diameters for the actuating heads	45 mm
Diameter of the knob	26 mm
Mounting diameter	22.3 mm
Thickness, of the front panel, minimum	1.5 mm
Thickness of the front panel, maximum	6 mm

Ambient conditions

Degree of protection	IP67 IP69K
Ambient temperature	+0 ... +80 °C

Scope of delivery

Note (scope of delivery, number and type)

Contact carrier SMF-SG is included in delivery

Pictures

Product picture (catalogue individual photo)



ID: khdanf01

| 380.4 kB | .jpg | 352.778 x 602.192 mm - 1000 x 1707 px - 72 dpi

| 58.0 kB | .png | 74.083 x 126.294 mm - 210 x 358 px - 72 dpi

| 34.7 kB | .jpg | 72.319 x 123.472 mm - 205 x 350 px - 72 dpi

Schmersal Ltd., Sparrowhawk Close, WR14 1GL Malvern

The details and data referred to have been carefully checked. Images may diverge from original. Further technical data can be found in the manual. Technical amendments and errors possible.

Generated on: 11/11/2024, 06:07