

Accessories

PROTECTIV CAP, BNC, plug (male)

61_BNC-0-0-1/-33_-

Properties

- Easy to work with
- High availability of products



General data	
Technology	Radio Frequency
Weight	0.0082 kg
Outer conductor material	Brass / SUCOPLATE (R) Plating
Body material	Brass / SUCOPLATE (R) Plating
Gasket material	VMQ (Silicone rubber)
Operation temperature	165 °C
Remarks	with chain (length 85 mm)

Ordering Information Table	
Item number	Item description
22540660	61_BNC-0-0-1/-33_-E

Accessories

PROTECTIV CAP, BNC, plug (male)

61_BNC-0-0-1/-33_-

Catalogue drawing

Accessories

PROTECTIV CAP, BNC, plug (male)

61_BNC-0-0-1/-33_-

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for
information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1814 / Date of publication: 20.06.2024 / uncontrolled copy