

Accessories

COAXIAL SHORT, SMA, 50 Ohm, plug (male)

64_SMA-50-0-1/111_N

Properties

- Easy to work with
- High availability of products



General data	
Technology	Radio Frequency
Weight	0.0023 kg
Centre contact material	Copper Beryllium Alloy / Gold Plating (Nickel underplated)
Outer conductor material	Copper Beryllium Alloy / Gold Plating (Nickel underplated)
Body material	Copper Beryllium Alloy / Gold Plating (Nickel underplated)
Gasket material	VMQ (Silicone rubber)
Operation temperature	-65 °C ... 165 °C

Accessories

COAXIAL SHORT, SMA, 50 Ohm, plug (male)

64_SMA-50-0-1/111_N

Catalogue drawing

This drawing is copyright information and must not be used for any other purpose than which it was supplied and must not be reproduced without written permission of the owner.
 Diese Zeichnung ist eine geistige Eigentum und darf nicht für andere Zwecke als für die, für die sie erstellt wurde, verwendet werden. Nachdruck, Vervielfältigung oder Verbreitung, auch auszugsweise, ist ohne schriftliche Genehmigung Huber+Suhner AG.

64 SMA 50 - 0 - 1		Datum	Kurz-/Vgsun
Erstellt	19.10.95	023/Tub	11E
Geprüft	Bo. G. S.	Bo. G. S.	SC
Freigebe	Bo. G. S.	Bo. G. S.	SC

SW 8
(.315 HEX.)

9.7
(.382)

M. 5:1	HUBER + SUHNER AG 9100 Herisau	4.13.06405_1	b
--------	-----------------------------------	--------------	---

H+S 701 448/95

Ordering Information Table	
Item number	Item description
22640161	64_SMA-50-0-1/111_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind. DOCUMENT PIM-P1788 / Date of publication: 09.08.2024 / uncontrolled copy