



Product: [83334E](#)

Electronic, 3 C #22 Str SPC, TFE Ins, OA SPC Brd, TFE Tape Jkt, MIL-W-16878/4 (Type E)

[Request Sample](#)

Product Description

High Temperature Electronic, 3 Conductor 22AWG (19x34) Silver Plated Copper, TFE Insulation, Overall Silver Plated Copper Braid(85%) Shield, TFE Tape Outer Jacket, MIL-W-16878/4 (Type E)

Technical Specifications

Product Overview

Suitable Applications:	MIL-W-16878/4 (Type E) Spec; Extreme High/Low Temperature Environments; up to 600V analog signals & voltage control
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	22 AWG	19x34	SC - Silvered Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PTFE - Polytetrafluoroethylene	0.010 in (0.25 mm)	0.050 in (1.3 mm)	White, Black, Red

Outer Shield

Shield Type	Material	Coverage
Braid	Silvered Copper (SC)	85%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PTFE - Polytetrafluoroethylene	0.011 in (0.28 mm)	0.150 in (3.81 mm)

Overall Cable Diameter (Nominal): 0.150 in (3.81 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	14.5 Ohm/1000ft	27.4 pF/ft (89.9 pF/m)	45.7 pF/ft (150 pF/m)	5 Amps per conductor @ 25°C

Voltage

Voltage Rating
600 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
200°C	-65°C to +200°C

Bend Radius

Stationary Min.	Installation Min.
1.5 in (38 mm)	1.5 in (38 mm)

Max. Pull Tension:	28.5 lbs (12.9 kg)
Bulk Cable Weight:	22 lbs/1000ft

Standards and Compliance

Sustainability:	CA Prop 65
CPR Compliance:	CPR Euroclass: Eca
NEMA Compliance:	NEMA HP3
Military Compliance:	MIL-W-16878/4 (Type E except stranding), (insulated conductors)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

History

Update and Revision:	Revision Number: 0.540 Revision Date: 04-19-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
83334E 009100	White	Reel	100 ft	612825204183	E
83334E 009500	White	Reel	500 ft	612825204206	E
83334E 0091000	White	Reel	1,000 ft	612825204190	E

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.