

TE Connectivity DEUTSCH Contacts

M29600 & M39029 Series



WIDE RANGE OF ELECTRICAL CONTACTS

TE DEUTSCH contacts – M29600 & M39029 series are used in a variety of military and commercial applications. These TE DEUTSCH electrical contacts are designed to meet MIL-C-39029 or MIL-C-29600 standards and can transfer power and/or signal. For full product details on TE DEUTSCH contacts – M29600 & M39029 series, please see the specifications below.

APPLICATIONS

- Electronic box
- Space & aerospace applications
- Military applications
- Industrial applications

FEATURES

- Signal or power transfer
- Data buss
- Mil-spec / ASN Standard

SELECT PART NUMBER

SPECIFICATION P/N	TE DEUTSCH P/N	BIN CODE		
M29600/23-606	12343-23	BLUE	BLACK	BLUE
M29600/23-607	12343-20	BLUE	BLACK	VIOLET
M29600/23-608	12343-16	BLUE	BLACK	GRAY
M29600/24-610	12341-23	BLUE	BROWN	BLACK
M29600/24-611	12341-20	BLUE	BROWN	BROWN
M29600/24-612	12341-16	BLUE	BROWN	RED
M39029/1-100	2560-214-1631*(L)	BROWN	BLACK	BLACK
M39029/1-101	2560-215-1631*(L)	BROWN	BLACK	BROWN
M39029/1-102	2560-216-1431*(L)	BROWN	BLACK	RED
M39029/1-103	2560-217-1231*(L)	BROWN	BLACK	ORANGE
M39029/1-507	2560-218-2031*(L)	GREEN	BLACK	VIOLET
M39029/4-110	0641-1-2031*(L)	BROWN	BROWN	BLACK
M39029/4-111	0641-2-1631*(L)	BROWN	BROWN	BROWN
M39029/4-112	109026-31	BROWN	BROWN	RED
M39029/4-113	0641-3-1231*(L)	BROWN	BROWN	ORANGE
M39029/4-114	109028-31*(L)	BROWN	BROWN	YELLOW
M39029/5-115	100503*(L)	BROWN	BROWN	GREEN
M39029/5-116	100504*(L)	BROWN	BROWN	BLUE
M39029/5-117	109027*(L)	BROWN	BROWN	VIOLET
M39029/5-118	100505*(L)	BROWN	BROWN	GRAY
M39029/5-119	109029*(L)	BROWN	BROWN	WHITE
M39029/10-521	7362-255-1601	GREEN	RED	BROWN
M39029/10-522	7362-226-1601	GREEN	RED	RED
M39029/11-144	2560-212-2231	BROWN	YELLOW	YELLOW
M39029/11-145	2560-212-2031*(L)	BROWN	YELLOW	GREEN
M39029/12-148	2562-209-2231*(L)	BROWN	YELLOW	GRAY
M39029/12-149	2562-209-2031*(L)	BROWN	YELLOW	WHITE
M39029/16-166	81542-238*(L)	BROWN	BLUE	BLUE
M39029/16-167	81542-23*(L)	BROWN	BLUE	VIOLET
M39029/16-168	81542-20*(L)	BROWN	BLUE	GRAY
M39029/16-169	81542-16*(L)	BROWN	BLUE	WHITE
M39029/16-170	81542-12*(L)	BROWN	VIOLET	BLACK
M39029/17-171	81543-238*(L)	BROWN	VIOLET	BROWN
M39029/17-172	81543-23*(L)	BROWN	VIOLET	RED
M39029/17-173	81543-20*(L)	BROWN	VIOLET	ORANGE
M39029/17-174	81543-16*(L)	BROWN	VIOLET	YELLOW
M39029/17-175	81543-12*(L)	BROWN	VIOLET	GREEN
M39029/18-176	81541-238*(L)	BROWN	VIOLET	BLUE
M39029/18-177	81541-23*(L)	BROWN	VIOLET	VIOLET
M39029/18-178	81541-20*(L)	BROWN	VIOLET	GRAY
M39029/18-179	81541-16*(L)	BROWN	VIOLET	WHITE
M39029/18-180	81541-12*(L)	BROWN	GRAY	BLACK
M39029/22-191	CTS-S22/22*(L)	BROWN	WHITE	BROWN
M39029/22-192	CTS-S20/20*(L)	BROWN	WHITE	RED
M39029/22-193	CTS-S16/16*(L)	BROWN	WHITE	ORANGE
M39029/22-605	CTS-S12/12*(L)	BLUE	BLACK	GREEN
M39029/28-211	6162-233-1277 (AU/NI)	RED	BROWN	BROWN
M39029/28-409	6162-234-1277 (AU/NI)	YELLOW	BLACK	WHITE
M39029/28-410	6162-235-1277 (AU/NI)	YELLOW	BROWN	BLACK
M39029/28-411	6162-236-1277 (AU/NI)	YELLOW	BROWN	BROWN
M39029/28-413 61	62-238-1277 (AU/NI)	YELLOW	BROWN	ORANGE
M39029/28-414	6162-239-1277 (AU/NI)	YELLOW	BROWN	YELLOW
M39029/28-415	6162-240-1277 (AU/NI)	YELLOW	BROWN	GREEN

*Various platings available, contact us.

SELECT PART NUMBER

SPECIFICATION P/N	TE DEUTSCH P/N	BIN CODE		
M39029/29-212	0660-206-1631*(L)	RED	BROWN	RED
M39029/29-213	0660-206-1282 (SILVER)	RED	BROWN	ORANGE
M39029/29-214	0660-206-08*	RED	BROWN	YELLOW
M39029/29-215	0660-206-04*	RED	BROWN	GREEN
M39029/29-216	0660-206-00*	RED	BROWN	BLUE
M39029/30-217	0662-212-1631*(L)	RED	BROWN	VIOLET
M39029/30-218	0662-207-1631*(L)	RED	BROWN	GRAY
M39029/30-219	0662-207-1282 (SILVER)	RED	BROWN	WHITE
M39029/30-220	0662-207-0882	RED	RED	BLACK
M39029/30-221	0662-207-0482	RED	RED	BROWN
M39029/30-222	0662-207-0082	RED	RED	RED
M39029/31-228	4160-203-1631*(L)	RED	RED	GRAY
M39029/31-229	4160-204-1631*(L)	RED	RED	WHITE
M39029/31-240	0004-058-100*(L)	RED	YELLOW	BLACK
M39029/31-241	CANCELED, REPLACED WITH /31-627	RED	YELLOW	BROWN
M39029/31-627	4160-202-2031*(L)	BLUE	YELLOW	VIOLET
M39029/32-247	4162-201-1631*(L)	RED	YELLOW	VIOLET
M39029/32-248	4162-202-1631*(L)	RED	YELLOW	GRAY
M39029/32-259	0007-008-100*(L)	RED	GREEN	WHITE
M39029/32-260	4109-207-2000*(L)	RED	BLUE	BLACK
M39029/56-348	38943-22*(L)	ORANGE	YELLOW	GRAY
M39029/56-351	38943-20*(L)	ORANGE	GREEN	BROWN
M39029/56-352	38943-16*(L)	ORANGE	GREEN	RED
M39029/56-353	38943-12*(L)	ORANGE	GREEN	ORANGE
M39029/57-354	38946-22*(L)	ORANGE	GREEN	YELLOW
M39029/57-357	38946-20*(L)	ORANGE	GREEN	VIOLET
M39029/57-358	38946-16*(L)	ORANGE	GREEN	GRAY
M39029/57-359	38946-12*(L)	ORANGE	GREEN	WHITE
M39029/58-360	38941-22	ORANGE	BLUE	BLACK
M39029/58-363	38941-20*(L)	ORANGE	BLUE	ORANGE
M39029/58-364	38941-16*(L)	ORANGE	BLUE	YELLOW
M39029/58-365	38941-12*(L)	ORANGE	BLUE	GREEN
M39029/63-368	2562-201-2031*(L)	ORANGE	BLUE	GRAY
M39029/64-369	2560-201-2031*(L)	ORANGE	BLUE	WHITE
M39029/75-416	6162-217-1277 (AU/NI)	YELLOW	BROWN	BLUE
M39029/75-417	6162-218-1277 (AU/NI)	YELLOW	BROWN	VIOLET
M39029/75-418	6162-219-1277 (AU/NI)	YELLOW	BROWN	GRAY
M39029/75-419	6162-220-1277 (AU/NI)	YELLOW	BROWN	WHITE
M39029/75-421	6162-222-1277 (AU/NI)	YELLOW	RED	BROWN
M39029/75-422	6162-223-1277 (AU/NI)	YELLOW	RED	RED
M39029/75-423	6162-224-1277 (AU/NI)	YELLOW	RED	ORANGE
M39029/76-424	6162-229-1677 (AU/NI)	YELLOW	RED	YELLOW
M39029/76-425	6162-230-1677 (AU/NI)	YELLOW	RED	GREEN
M39029/76-426	6162-231-1677 (AU/NI)	YELLOW	RED	BLUE
M39029/76-427	6162-232-1677 (AU/NI)	YELLOW	RED	VIOLET
M39029/77-428	6162-213-1677 (AU/NI)	YELLOW	RED	GRAY
M39029/77-429	6162-214-1677 (AU/NI)	YELLOW	RED	WHITE
M39029/77-430	6162-215-1677 (AU/NI)	YELLOW	ORANGE	BLACK
M39029/77-431	6162-216-1677 (AU/NI)	YELLOW	ORANGE	BROWN
M39029/78-432	6162-253-1677 (AU/NI)	YELLOW	ORANGE	RED
M39029/78-433	6162-254-1677 (AU/NI)	YELLOW	ORANGE	ORANGE
M39029/78-434	6162-255-1677 (AU/NI)	YELLOW	ORANGE	YELLOW
M39029/78-435	6162-256-1677	YELLOW	ORANGE	GREEN

*Various platings available, contact us.

SELECT PART NUMBER

SPECIFICATION P/N	DEUTSCH P/N	BIN CODE		
M39029/83-450	2560-221-2031*(L)	YELLOW	GREEN	BLACK
M39029/83-451	2560-222-2031*(L)	YELLOW	GREEN	BROWN
M39029/83-508	2560-220-2031*(L)	GREEN	BLACK	GRAY
M39029/84-452	2562-214-2031*(L)	YELLOW	GREEN	RED
M39029/84-453	2562-215-2031*(L)	YELLOW	GREEN	ORANGE
M39029/84-509	2562-213-2031*(L)	GREEN	BLACK	WHITE
M39029/90-529	6162-283-0877	GREEN	RED	WHITE
M39029/91-530	6162-284-0877	GREEN	ORANGE	BLACK
M39029/101-553	1662-213-2031*(L)	GREEN	GREEN	ORANGE
M39029/101-554	1662-213-1631*(L)	GREEN	GREEN	YELLOW
M39029/102-558	6162-324-1231	GREEN	GREEN	GRAY
M39029/103-559	6162-325-1231	GREEN	GREEN	WHITE
M39029/106-614	12333-22*(L)	BLUE	BROWN	YELLOW
M39029/106-615	12333-20*(L)	BLUE	BROWN	GREEN
M39029/106-616	12333-16*(L)	BLUE	BROWN	BLUE
M39029/106-617	12333-12*(L)	BLUE	BROWN	VIOLET
M39029/107-620	12331-22	BLUE	RED	BLACK
M39029/107-621	12331-20*(L)	BLUE	RED	BROWN
M39029/107-622	12331-16*(L)	BLUE	RED	RED
M39029/107-623	12331-12*(L)	BLUE	RED	ORANGE
02003-926 (DSCC PART NUMBER)	6162-328-1277 (AU/NI)	WHITE	RED	BLUE
02004-936 (DSCC PART NUMBER)	6162-330-1277 (AU/NI)	WHITE	ORANGE	BLUE
M55302/65-02	2562-236-2231	N/A	N/A	N/A

*Various platings available, contact us.