

Part number

APV 14



Painted distribution box, AP series, external dimensions 168x192x80 mm / internal dimensions 152x176x65 mm

Product description		Material properties	
Product type	Painted distribution box	Main material	Aluminium die-cast
Series	AP	Other materials	Gasket: Polyurethane (PUR) Screws: galvanized steel
Size	External dimensions 168x192x80 mm / internal dimensions 152x176x65 mm	Colour	RAL 7040 grey
Technical data		RoHs conformity	Compliant with exemption 6(c): copper alloy containing up to 4% lead by weight
IP degree of protection	IP66 / IP67	China RoHs - EFUP	50
Further technical details		REACH SVHC substances	Yes Lead
Weight	870,00 g	SCIP number	A4d990c2-7936-4d11-a722-eb8d5d39ca82
Operating temperature range (min, max)	-40°C...+110°C	General ordering information	
		EAN13 code	8015747001816
Packaging Information			
Packaging length	420,00 mm	Packaging height	350,00 mm
Packaging width	395,00 mm	Packaging weight	18,20 kg
Packaging volume	58,07 dm ³	Packaging description	Carton box
Packaging quantity	20 Pcs	Packaging EAN code	8015747001823
Sub-packaging weight	0,91 kg	Sub-packaging description	Plastic packaging
Sub-packaging quantity	1 Pcs	Sub-packaging EAN barcode	8015747200035

Part number

APV 14



Notes

California Proposition 65 Information



WARNING

This product can expose you to lead and its compounds, known to the State of California to cause cancer and/or reproductive toxicity. For more information go to www.P65Warnings.ca.gov.
