

Part number  
**APV 20**



Painted distribution box, AP series, external dimensions 264x314x122 mm / internal dimensions 243x292x104 mm

Product description	
<b>Product type</b>	Painted distribution box
<b>Series</b>	AP
<b>Size</b>	External dimensions 264x314x122 mm / internal dimensions 243x292x104 mm
Technical data	
<b>IP degree of protection</b>	IP66 / IP67
Further technical details	
<b>Weight</b>	2.565,00 g
<b>Operating temperature range (min, max)</b>	-40°C...+110°C

Material properties	
<b>Main material</b>	Aluminium die-cast
<b>Other materials</b>	Gasket: Polyurethane (PUR) Screws: galvanized steel
<b>Colour</b>	RAL 7040 grey
<b>RoHs conformity</b>	Compliant with exemption 6(c): copper alloy containing up to 4% lead by weight
<b>China RoHs - EFUP</b>	50
<b>REACH SVHC substances</b>	Yes Lead
<b>SCIP number</b>	A4d990c2-7936-4d11-a722-eb8d5d39ca82
General ordering information	
<b>EAN13 code</b>	8015747001854
Packaging Information	
<b>Packaging length</b>	390,00 mm
<b>Packaging height</b>	330,00 mm
<b>Packaging width</b>	550,00 mm
<b>Packaging weight</b>	16,25 kg
<b>Packaging volume</b>	70,79 dm <sup>3</sup>
<b>Packaging description</b>	Carton box
<b>Packaging quantity</b>	6 Pcs
<b>Packaging EAN code</b>	8015747113120
<b>Sub-packaging weight</b>	2,71 kg
<b>Sub-packaging description</b>	Plastic packaging
<b>Sub-packaging quantity</b>	1 Pcs
<b>Sub-packaging EAN barcode</b>	8015747283205