



Features

- Available in Tin Copper or Topcoat
- PVC (Polyvinylchloride) Insulation
- 1007 80°C & 1569 105°C, 300V
- UL, CSA VW-1 AWM I A/B FT-1

Specification Table

Part Number	Colour	Construction	Product Type	Insulation	Insulation (in)	Nom. OD (in)	Length (ft)
24-15410	Black	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15411	Brown	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15412	Red	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15413	Orange	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15414	Yellow	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15415	Green	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15416	Blue	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15417	Violet	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15418	Grey	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15419	White	22 (Solid) TC	1569 / 1007	PVC	0.016	0.057	25
24-15430	Black	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15431	Brown	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15432	Red	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15433	Orange	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15434	Yellow	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15435	Green	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15436	Blue	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15437	Violet	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15438	Grey	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15439	White	24 (Solid) TC	1569 / 1007	PVC	0.016	0.053	25
24-15450	Black	26 (Solid) TC	1569 / 1007	PVC	0.015	0.048	25
24-15452	Red	26 (Solid) TC	1569 / 1007	PVC	0.015	0.048	25
24-15453	Orange	26 (Solid) TC	1569 / 1007	PVC	0.015	0.048	25
24-15454	Yellow	26 (Solid) TC	1569 / 1007	PVC	0.015	0.048	25
24-15455	Green	26 (Solid) TC	1569 / 1007	PVC	0.015	0.048	25
24-15456	Blue	26 (Solid) TC	1569 / 1007	PVC	0.015	0.048	25
24-15459	White	26 (Solid) TC	1569 / 1007	PVC	0.015	0.048	25
24-15390	Black	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25

Hook-up Wire

multicompPRO

Part Number	Colour	Construction	Product Type	Insulation	Insulation (in)	Nom. OD (in)	Length (ft)
24-15391	Brown	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15392	Red	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15393	Orange	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15394	Yellow	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15395	Green	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15396	Blue	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15397	Violet	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15398	Grey	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15399	White	20 (Solid) TC	1569 / 1007	PVC	0.016	0.064	25
24-15150	Black	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15140	Black	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15141	Brown	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15151	Brown	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15142	Red	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15152	Red	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15153	Orange	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15143	Orange	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15144	Yellow	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15154	Yellow	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15145	Green	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15155	Green	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15156	Blue	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15146	Blue	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15147	Violet	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15157	Violet	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15148	Grey	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15158	Grey	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15159	White	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15149	White	26 (7x34) TC	1569 / 1007	PVC	0.016	0.051	25
24-15120	Black	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15130	Black	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15121	Brown	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15131	Brown	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15132	Red	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15122	Red	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15133	Orange	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15123	Orange	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15124	Yellow	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

Hook-up Wire

multicompPRO

Part Number	Colour	Construction	Product Type	Insulation	Insulation (in)	Nom. OD (in)	Length (ft)
24-15134	Yellow	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15125	Green	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15135	Green	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15126	Blue	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15136	Blue	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15127	Violet	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15137	Violet	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15138	Grey	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15128	Grey	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15139	White	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15129	White	24 (7x32) TC	1569 / 1007	PVC	0.016	0.056	25
24-15110	Black	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15100	Black	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15101	Brown	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15111	Brown	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15102	Red	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15112	Red	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15103	Orange	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15113	Orange	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15104	Yellow	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15114	Yellow	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15115	Green	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15105	Green	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15106	Blue	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15116	Blue	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15107	Violet	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15117	Violet	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15118	Grey	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15108	Grey	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15109	White	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15119	White	22 (7x30) TC	1569 / 1007	PVC	0.016	0.062	25
24-15080	Black	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15090	Black	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15081	Brown	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15091	Brown	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15082	Red	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15092	Red	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15083	Orange	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

Hook-up Wire

multicompPRO

Part Number	Colour	Construction	Product Type	Insulation	Insulation (in)	Nom. OD (in)	Length (ft)
24-15093	Orange	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15084	Yellow	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15094	Yellow	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15085	Green	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15095	Green	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15086	Blue	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15096	Blue	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15087	Violet	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15097	Violet	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15098	Grey	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15088	Grey	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15089	White	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15099	White	20 (10x30) TC	1569 / 1007	PVC	0.016	0.07	25
24-15060	Black	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15070	Black	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15061	Brown	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15071	Brown	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15071	Brown	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15062	Red	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15072	Red	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15073	Orange	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15063	Orange	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15073	Orange	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15064	Yellow	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15074	Yellow	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15075	Green	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15065	Green	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15076	Blue	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15076	Blue	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15066	Blue	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15066	Blue	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15067	Violet	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15077	Violet	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15078	Grey	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15068	Grey	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15079	White	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15069	White	18 (16x30) TC	1569 / 1007	PVC	0.016	0.08	25
24-15050	Black	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

Part Number	Colour	Construction	Product Type	Insulation	Insulation (in)	Nom. OD (in)	Length (ft)
24-15052	Red	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15053	Orange	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15054	Yellow	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15054	Yellow	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15055	Green	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15056	Blue	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15056	Blue	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15059	White	16 (26x30) TC	1569 / 1007	PVC	0.016	0.092	25
24-15370	Black	18 (Solid) TC	1569 / 1007	PVC	0.016	0.072	25
24-15371	Brown	18 (Solid) TC	1569 / 1007	PVC	0.016	0.072	25
24-15372	Red	18 (Solid) TC	1569 / 1007	PVC	0.016	0.072	25
24-15374	Yellow	18 (Solid) TC	1569 / 1007	PVC	0.016	0.072	25
24-15375	Green	18 (Solid) TC	1569 / 1007	PVC	0.016	0.072	25
24-15376	Blue	18 (Solid) TC	1569 / 1007	PVC	0.016	0.072	25
24-15379	White	18 (Solid) TC	1569 / 1007	PVC	0.016	0.072	25

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.