

Product Specification PDF

Date	Correct as of 6th Aug 2019
Brand	C.K
Product	T3766DF 110
Description	SensoPlus Side Cutter 110mm
Barcode	5013969973518
Commodity code	8203200000
Country of origin	DE



Features & Benefits	~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ Precision box joint construction for permanent, adjustment free jaw alignment ~ Induction hardened jaws for outstanding long term performance ~ Mirror polished surface eliminates the risk of damage from flaking chrome ~ Spot welded double leaf springs for consistent, repetitive action ~ Ergonomically designed dual component handles for increased comfort & control ~ Fully ESD compliant for safe use on sensitive electronic components ~ According to IEC 61340 5.1 & 5.2 ~ Tapered and relieved head for confined spaces ~ Bevel: Full Flush Cut ~ Length of cutting edges: 9 mm ~ Overall length: 120 mm ~ Cutting capacities wire: Hard: ~ mm / Medium Hard: 0,8 mm / Soft: 1,5 mm
Applicable Standards	IEC 61340 5.1 & 5.2
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	120
Width mm	75	60	0	380
Depth mm	6	25	0	300
Height mm	120	160	0	360
Weight	43	62	0	8.1
Packaging Information	Card use	Box	0	Case
	Card gms	18	0	675
	Plastic use	Bag	0	-
	Plastic gms	1	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0