

Product Specification PDF

Date	Correct as of 6th Aug 2019
Brand	C.K
Product	T3886
Description	Ecotronic ESD Side Cutters (Slim, Relieved)
Barcode	5013969938869
Commodity code	8203200000
Country of origin	TW



Features & Benefits

Lightweight, precision side cutters for fine cutting applications Suitable for cutting soft copper wires of up to 1.3mmØ / 16AWG Slim, tapered and relieved head for access in narrow and confined spaces Sharp, precision ground cutting edges with a full flush cut Special tool steel blade, hardened for long-term cutting performance Electro-static discharging handles ~ dissipative 10? Contoured, dual component handle design for comfortable working Black oxidised finish for corrosion resistance and reduced glare Smooth-action return spring for convenience during repetitive work Joint with durable stainless steel rivet Technical information: Total length: 139 mm Blade length: 10 mm Cutting angle: 21° Head Height (from joint to tip): 21 mm Head Width (Widest point): 11 mm Steel Thickness: 2,5 mm Cutting Capacity (Copper only) : 1,3 mm / 16 AWG

Applicable Standards

IEC 61340 5.1 & 5.2

Health & Safety

None applicable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	120
Width mm	139	220	21.6	470
Depth mm	70	80	8.4	470
Height mm	20	2.5	10.8	240
Weight	76	91	615	13.3
Packaging Information	Card use	0	Box	Case
	Card gms	0	69	1012.5
	Plastic use	Blister	0	-
	Plastic gms	15	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0