PNOZ X2.8P 24VACDC 3n/o 1n/c 777301

Safety relay (standalone), inputs: 1/2-channel wiring with/without detection of shorts across contacts, outputs: 3 N/O, 1 N/C, automatic/manual start, UB 24 V AC/DC, width: 22.5 mm, plug-in screw terminals, monitoring of E-STOP, safety gates.

Technical details

General data	
Approval:	CCC, CE, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV
Technical data Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	0
RoHS exceptions:	0
RoHS except.s acc. to direct.:	7A, 6C, 7C I
REACh compliance:	1
REACh included substances:	Blei, Bleioxid
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1, 1317-36-8
SCIP entry available:	yes
WEEE classification (08/2018):	U_KATEGORIE_5
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449

UNSPSC 25:	39122331
GTIN:	4046548009897
Volume:	0.301
Harmonized System Code:	85364900
Type of tariff number:	TARIC
Use of customs tariff number:	export, Import
Quantity per packaging unit:	1

Optional accessories

374280 PNOZ X Set plug in screw terminals P1+P2