

# Eaton 180LET

Catalog Number: 180LET

Eaton Bussmann series high speed British standard fuse, 180A, 250 VAC/150 VDC (UL), Class aR, 200 kA RMS Sym.



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series high speed british standard fuse	180LET
	<b>EAN</b>
	5027590466134
<b>UPC</b>	<b>Product Length/Depth</b>
051712832083	55 mm
<b>Product Height</b>	<b>Product Width</b>
18 mm	18 mm
<b>Product Weight</b>	<b>Compliances</b>
32 g	CE Marked
	RoHS Compliant

## Certifications

IEC Rated  
UL Recognized  
Designed and tested to BS88 part 4  
UL recognized  
IEC 60269-4

## Electrical data

### Amperage Rating

180 A

### Voltage rating

250 V

### Rated voltage AC

250 V

### Rated voltage DC

150 V

### Interrupt rating

200 kA RMS Sym, 50 kA DC at 150 Vdc

### Class

Class aR

### Pre arc (I2T)

1600

### Clearing (I2T)

29000

### Watt losses

21 W

## Product specifications

### Application

Semiconductor, DC Common bus, DC drives, power converters/rectifiers

### Fuse indicator

None

## Compatible Trip indicator/Microswitch

### Suitable for

EC-250 Trip indicator kit (indicator + clips)

TI250 Fuse indicator

MAI Microswitch/adaptor

MBI Microswitch/adaptor

## Resources

### Brochures

[eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf](#)

### Catalogues

[IEC high speed fuse links](#)

### Certification reports

[DA-DC-00004685](#)

[DA-DC-00004682](#)

### Technical data sheets

[720004 LCT, LET, LMMT, LMT](#)