

Model: MW3302GT

# TECHNICAL DATA

page2

**Model Number:** MW3302GT

**Reference Number:** MW3302GT

**Type** Switching Power Supply

## Electrical Data

|                   |                            |   |
|-------------------|----------------------------|---|
| <b>Input</b>      | Input Voltage/Frequency    | 100-240V□60/50Hz                                |
|                   | Input Power Current        | 150mA   |
| <b>Output</b>     | Rated Output Voltage       | 5V  |
|                   | Rated Output Load Current  | 1000mA  |
|                   | Rated Output Power         | 5.0VA   |
| <b>Resistance</b> | Insulation Resistance      | 100MΩ(measured with 500V DC voltage)            |
|                   | Withstand Voltage (Hi-Pot) | AC 3000V 50Hz for 1minute or AC 3300V 2 Seconds |

## Mechanical Data

|                              |                               |
|------------------------------|-------------------------------|
| Supply Connection Type       | SCHUKO type MWGT-1DIN49 464/F |
| Primary Turns & Wire Gauge   | Primary 130T/0.25mm           |
| Secondary Turns & Wire Gauge | 7T/0.50mm Triple-Insulated    |
| Core                         | Magnetic Core                 |
| Output Plug Dimensions       | USB                           |
| Polarity                     | -----                         |
| Unit Weight                  | 130g                          |
| Dimensions                   | 68(L)×52.5(W)×55(H)           |