



Sample photo

Order symbol: CAB PC 504020 T3B
Product nbr: 8113062
Description: Cabinet, PC
Remarks: Locks on the long side

EAN: 6418074020376
EI. number:
 Finland 3424174
 Denmark 8212019276
 Italy 7822060
 Sweden 2539955

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		L	W	H	Rating:
mm:		500	400	200	Ingress Protection (EN 60529): IP 65
inch:		19.7	15.7	7.9	Impact Resistance (EN 50102): IK 08
Materials:					Electrical insulation: Totally insulated
Material:	PC				Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035				UV resistance: UL 508
Cover colour:	Smoked grey				Flammability Rating (UL 746 C 5): UL 94 V5
Gasket material:	EPDM				Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					UL Type: UL TYPE 1, 4, 4X, 12, 13
Short term:	-40 ... 120 °C				Certificates:
Continuous:	-40 ... 80 °C				Germanischer Lloyd (GL)
Short term:	-40 ... 250 °F				Underwriters Laboratories
Continuous:	-40 ... 175 °F				Fimko
Accessories:					Lloyds Register of Shipping (LR)
EKIV 54	Mounting plate				Europe EN 50298 1998
EKIV 37	DIN-35 Mounting rail				UL Canada
EKIV 47	DIN-35 Mounting rail				Gost R
FP A 54	Swing-out door, aluminium				
FP 54	Front plate				
FP 18X2-54	Front Plate				
DRF 54	DIN rail frame set				

