

## Samsung FINO 800

Camera - Compact - 135mm - with Zoom - with Built-in Flash - with Red Eye Reduction

### Product Features

- **Product Description:** Samsung Fino 800 - Point & Shoot / Zoom camera - 35mm
- **Camera Type:** Point & Shoot / Zoom camera
- **Dimensions (WxDxH):** 11.7 cm x 4.7 cm x 7.1 cm
- **Weight:** 200 g
- **Camera Format:** 35mm
- **Lens Aperture:** F/6.3-12.3
- **Focus Adjustment:** Automatic
- **Optical Zoom:** 2.1
- **Focal Length:** 38 mm - 80 mm
- **Exposure Range:** 1/250 sec - 1/3 sec
- **Film Advance:** Automatic
- **Viewfinder:** Real-image zoom
- **Camera Flash:** Built-in flash
- **Timer Functions:** Self timer
- **Red Eye Reduction:** Built-in
- **Battery:** 2 x battery - AA type



---

## Technical Details

### Main Specifications

- **Product Description:** Samsung Fino 800 - Point & Shoot / Zoom camera - 35mm
- **Camera Type:** Point & Shoot / Zoom camera
- **Dimensions (WxDxH):** 11.7 cm x 4.7 cm x 7.1 cm
- **Weight:** 200 g
- **Camera Format:** 35mm
- **Lens Aperture:** F/6.3-12.3
- **Focus Adjustment:** Automatic
- **Optical Zoom:** 2.1
- **Focal Length:** 38 mm - 80 mm
- **Exposure Range:** 1/250 sec - 1/3 sec
- **Film Advance:** Automatic
- **Viewfinder:** Real-image zoom
- **Camera Flash:** Built-in flash
- **Timer Functions:** Self timer
- **Red Eye Reduction:** Built-in
- **Battery:** 2 x battery - AA type

### Extended Specifications

#### General

- **Depth:** 4.7 cm
- **Height:** 7.1 cm
- **Weight:** 200 g
- **Width:** 11.7 cm

#### Battery

- **Required Qty:** 2
- **Type:** Battery - AA type

#### Camera

- **Exposure Range:** 1/250 sec - 1/3 sec
- **Features:** Autofocus lock

#### Camera Flash

- **Camera Flash:** Built-in flash
- **Flash Modes:** Fill-in mode, auto mode, flash OFF mode, red-eye reduction
- **Red Eye Reduction:** Built-in
- **Shooting Distance:** 2.9 m : ISO 100 ( wide lens ) | 1.5 m : ISO 100 ( tele lens ) | 4.2 m : ISO 200 ( wide lens ) | 2.2 m : ISO 200 ( tele lens ) | 5.9 m : ISO 400 ( wide lens ) | 3 m : ISO 400 ( tele lens )

#### Lens System

- **Focal Length:** 38 mm - 80 mm
- **Focus Adjustment:** Automatic
- **Lens Aperture:** F/6.3-12.3
- **Lens Construction:** 4 group(s) / 4 element(s)
- **Min Focus Range:** 1 m
- **Optical Zoom:** 2.1 x
- **Type:** Zoom lens

#### Viewfinder

- **Field Coverage:** 80%
- **LED Information:** Flash ready, autofocus ready
- **Magnification:** 0.32 - 0.64x
- **Viewfinder Frames:** Autofocus frame, close-up correction frame