

tyco / *Electronics*



Stainless Steel Cable Ties

Stainless Steel Cable Ties (Roller Ball)

Type : Roller Ball Uncoated
Material : Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Size (mm)	Pack Qty.
BU46-100	1634259-1	100 x 4.6	100
BU46-150	1634259-2	150 x 4.6	100
BU46-200	1634259-3	200 x 4.6	100
BU46-260	I-1634259-7	260 x 4.6	100
BU46-360	1634259-4	360 x 4.6	100
BU46-520	1634259-5	520 x 4.6	100
BU46-620	1634259-6	620 x 4.6	100
BU46-840	1634259-7	840 x 4.6	100
BU46-1000	1634259-8	1000 x 4.6	100
BU76-100	1634259-9	100 x 7.9	50
BU76-150	I-1634259-0	150 x 7.9	50
BU76-200	I-1634259-1	200 x 7.9	50
BU76-260	I-1634259-8	260 x 7.9	50
BU76-360	I-1634259-2	360 x 7.9	50
BU76-520	I-1634259-3	520 x 7.9	50
BU76-620	I-1634259-4	620 x 7.9	50
BU76-840	I-1634259-5	840 x 7.9	50
BU76-1000	I-1634259-6	1000 x 7.9	50

Loop Tensile Strength: 4.6 mm width 445 N (100 Lbs) - 7.9 mm width 1112 N (250 Lbs)



R O L L E R B A L L

Type : Roller Ball Coated
Material : Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Size (mm)	Pack Qty.
BC46-100	1634260-1	100 x 4.6	100
BC46-150	1634260-2	150 x 4.6	100
BC46-200	1634260-3	200 x 4.6	100
BC46-260	I-1634260-7	260 x 4.6	100
BC46-360	1634260-4	360 x 4.6	100
BC46-520	1634260-5	520 x 4.6	100
BC46-620	1634260-6	620 x 4.6	100
BC46-840	1634260-7	840 x 4.6	100
BC46-1000	1634260-8	1000 x 4.6	100
BC76-100	1634260-9	100 x 7.9	50
BC76-150	I-1634260-0	150 x 7.9	50
BC76-200	I-1634260-1	200 x 7.9	50
BC76-260	I-1634260-8	260 x 7.9	50
BC76-360	I-1634260-2	360 x 7.9	50
BC76-520	I-1634260-3	520 x 7.9	50
BC76-620	I-1634260-4	620 x 7.9	50
BC76-840	I-1634260-5	840 x 7.9	50
BC76-1000	I-1634260-6	1000 x 7.9	50

Loop Tensile Strength: 4.6 mm width 445 N (100 Lbs) - 7.9 mm width 1112 N (250 Lbs)



Ordering Example

B	U	4	6	-680
Tie Type B - S.S.Ties, Roller Ball Type	Finish U - Uncoated C - Coated	Width 4 - 4.6mm 7 - 7.9mm	Grade 6 - SS 316	Length 100 to 1000, prefixed with "I."



Stainless Steel Cable Ties (Ladder)

Type : Ladder Uncoated
Material : Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Size (mm)	Pack Qty.
LU76-150	1814426-1	150 x 7.0	100
LU76-225	1814426-3	225 x 7.0	100
LU76-300	1814426-5	300 x 7.0	100
LU76-450	1814426-7	450 x 7.0	100
LU76-610	1814426-9	610 x 7.0	100
LUI26-150	1-1814426-2	150 x 12	50
LUI26-225	1-1814426-4	225 x 12	50
LUI26-300	1-1814426-6	300 x 12	50
LUI26-450	1-1814426-8	450 x 12	50
LUI26-610	2-1814426-0	610 x 12	50

Loop Tensile Strength: 7 mm width 445 N (100 Lbs) - 12 mm width 1112 N (250 Lbs)

L A D D E R



Type : Ladder Coated
Material : Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Size (mm)	Pack Qty.
LC76-150	1814427-1	150 x 7.0	100
LC76-225	1814427-3	225 x 7.0	100
LC76-300	1814427-5	300 x 7.0	100
LC76-450	1814427-7	450 x 7.0	100
LC76-610	1814427-9	610 x 7.0	100
LCI26-150	1-1814427-2	150 x 12	50
LCI26-225	1-1814427-4	225 x 12	50
LCI26-300	1-1814427-6	300 x 12	50
LCI26-450	1-1814427-8	450 x 12	50
LCI26-610	2-1814427-0	610 x 12	50

Loop Tensile Strength: 7 mm width 445 N (100 Lbs) - 12 mm width 1112 N (250 Lbs)

Ordering Example

L	C	7	6	-680
Tie Type	Finish	Width	Grade	Length
L - S.S Ties, Ladder Type	U - Uncoated C - Coated	7 - 7mm 12 - 12mm	6 - SS 316	150 to 1000, prefixed with "-"

Stainless Steel Cable Ties (Releasable)

Type : Releasable Uncoated
Material : Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Size (mm)	Pack Qty.
RU56-150	1634261-1	150 x 5.0	100
RU56-230	1634261-2	230 x 5.0	100
RU56-330	1634261-3	330 x 5.0	100
RU56-450	1634261-4	450 x 5.0	100
RU56-600	1634261-5	600 x 5.0	100
RU56-750	1634261-6	750 x 5.0	100
RU56-900	1634261-7	900 x 5.0	100
RU106-150	1634261-8	150 x 10	50
RU106-230	1634261-9	230 x 10	50
RU106-330	1-1634261-0	330 x 10	50
RU106-450	1-1634261-1	450 x 10	50
RU106-600	1-1634261-2	600 x 10	50
RU106-750	1-1634261-3	750 x 10	50
RU106-900	1-1634261-4	900 x 10	50

Loop Tensile Strength: 5 mm width 1334 N (300 Lbs) - 10 mm width 2000 N (450 Lbs)



R E L E A S A B L E

Type : Releasable Coated
Material : Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Size (mm)	Pack Qty.
RC56-150	1634262-1	150 x 5.0	100
RC56-230	1634262-2	230 x 5.0	100
RC56-330	1634262-3	330 x 5.0	100
RC56-450	1634262-4	450 x 5.0	100
RC56-600	1634262-5	600 x 5.0	100
RC56-750	1634262-6	750 x 5.0	100
RC56-900	1634262-7	900 x 5.0	100
RC106-150	1634262-8	150 x 10	50
RC106-230	1634262-9	230 x 10	50
RC106-330	1-1634262-0	330 x 10	50
RC106-450	1-1634262-1	450 x 10	50
RC106-600	1-1634262-2	600 x 10	50
RC106-750	1-1634262-3	750 x 10	50
RC106-900	1-1634262-4	900 x 10	50

Loop Tensile Strength: 5 mm width 1334 N (300 Lbs) - 10 mm width 2000 N (450 Lbs)



Ordering Example

R	U	5	6	-900
Tie Type	Finish	Width	Grade	Length
R - S.S.Ties, Releasable Type	U - Uncoated C - Coated	5 - 5mm 10 - 10mm	6 - SS 316	150 to 900, prefixed with "-"

Beta Ties Light Duty Stainless Steel Ties

Type : Critchley
Material : Uncoated Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Strap Length		Strap Width		Loop Tensile* Strength (N) Tamped	Maximum Bundle Diameter		Packed
		inches	mm	inches	mm		inches	mm	
18199999	1-1988858-2	5.5	140	0.2	5.0	1200	1.37	35	250

* Minimum Values



- Material - 316 Stainless Steel
- Standard Colour - Metallic
- Limited Fire Hazard
- One-Piece Construction
- Suitable for Hostile Environments



Type : Critchley
Material : Nylon II Coated Stainless Steel Grade 316



Sales Part No.	Tyco Part No.	Sales Part No.	Tyco Part No.	Strap Length**		Loop Tensile* Strength (N) Tamped		Maximum Bundle Dia.		Colour#	Packed
				inches	mm	6mm Strap Width	9.5mm Strap Width	inches	mm		
1820	7-1200199-6	1830	9-1200203-7	9	229	1000	1550	2.3	58	Black	100
1821	2-1200196-2	1831	9-1200202-3	12	305	1050	1450	3.3	84	Black	100
1822	2-1200189-8	1832	6-1200194-0	18	457	1250	1475	5.2	132	Black	100
-	-	1833	6-1200190-3	24	610	-	1500	7.1	180	Black	50

* Minimum Values ** Length Excluding Buckle #Other Colours Available - Subject to Quotation



- Standard Colour - Black
- Service Temperature - Up to +80°C
- Limited Fire Hazard
- One-Piece Construction

Stainless Steel Cable Tie Tooling



Sales Part No: EPGSS20A
Tyco Part No: 1814428-1



Sales Part No: EPGSS10A
Tyco Part No: 1814429-1

- Adjustable tensioning tool with automatic cut off for unwanted tie tail
- Thickness of tie:- up to 3.0mm
- Width of tie:- up to 7.9mm
- Manual tensioning tool with cut off for unwanted tie tail
- Thickness of tie:- up to 3.0mm
- Width of tie:- up to 7.9mm