

---

Item no.: 733-332  
Product description: HEADER; STRAIGHT SOLDER PIN 0.8x0.8 MM; 2 POLE; PIN SPACING 2.5 MM / 0.098 IN; 100% PROTECTED AGAINST MISMATING; MATING DIRECTION PERPENDICULAR TO PCB

---



Packing unit 200 pieces

Pin spacing from	2,5 mm
Pin spacing from	0,098 in
pole count	2
Measured voltage EN	250 V
Measured shock voltage	2,5 kV
Pollution degree	2
Current intensity EN	4 A
Voltage CSA	150 V
Current CSA	4 A
Voltage UL	150 V
Voltage UL	250 V
Current UL	4 A
Weight	0,38 g
Color	light grey
Height	8,9 mm
Height	0,35 in
Width	7,5 mm
Width	0,295 in
Depth	7,8 mm
Depth	0,307 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
733-332	ABS	04-HG469925-PDA	250	4	
733-332	BV	11915/A0	250	4	
733-332	CSA	154112-1465035	150	4	28-20
733-332	CSM	017956	250	4	0,8-0,5
733-332	DNV	E-6997	250	4	
733-332	GL	17296-00HH	250	4	
733-332	KEMA	2077592.01	250	4	
733-332	LR	96/20035	250	6	
733-332	RMR	11130002	250	4	
733-332	RosTesT	B09523	250	4	
733-332	UL	E45171	250	4	0,8x0,8
733-332	UL	E45172	150	4	28-20

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected