
Item no.: 733-364
Product description: HEADER; RIGHT ANGLE SOLDER PIN 0.8x0.8 MM; 4 POLE;
PIN SPACING 2.5 MM / 0.098 IN; 100% PROTECTED
AGAINST MISMATING; MATING DIRECTION PARALLEL TO
PCB



Packing unit 200 pieces

Pin spacing from	2,5 mm
Pin spacing from	0,098 in
pole count	4
Measured voltage EN	250 V
Measured shock voltage	2,5 kV
Pollution degree	2
Current intensity EN	4 A
Voltage CSA	150 V
Current CSA	4 A
Voltage UL	150 V
Voltage UL	250 V
Current UL	4 A
Weight	0,712 g
Color	light grey
Height	7,8 mm
Height	0,307 in
Width	12,5 mm
Width	0,492 in
Depth	8,9 mm
Depth	0,35 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
733-364	ABS	04-HG469925-PDA	250	4	
733-364	BV	11915/A0	250	4	
733-364	CCA	NL5640	250	4	
733-364	CSA	154112-1465035	150	4	28-20
733-364	CSM	017956	250	4	0,8-0,5
733-364	DNV	E-6997	250	4	
733-364	GL	17296-00HH	250	4	
733-364	KEMA	2077592.01	250	4	
733-364	LR	96/20035	250	6	
733-364	RMR	11130002	250	4	
733-364	RosTesT	B09523	250	4	
733-364	UL	E45171	250	4	0,8x0,8
733-364	UL	E45172	150	4	28-20

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected