



- 1. CABLE: NO UL, 28AWG(7/0.127), TINNED AND STRANDED COPPER WIRE  
INSULATOR: PVC, ID: 0.85mm, CABLING: 7C+DRAIN WIRE  
SHIELD: AL/MY COVERAGE  
JACKET: PVC, COMPLIANCE ROHS, COLOR: BEIGE, D.D: 5mm
- 2. 2PCS CONNECTOR: D-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR  
INSULATOR: P.B.T.+GLASS FIBER, COLOR: BLUE  
CONTACT: COPPER ALLOY, GOLD FLASH OVER NICKEL PLATED  
SHELL: NICKEL PLATED.  
CONNECTOR COMPLIANCE ROHS
- 3. HOOD: PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER  
ON INNER MOLD AND INJECTION OUTER MOLD WITH  
THUMB SCREW #4-40 UNC  
COLOR: BEIGE, COMPLIANCE ROHS
- 4. Fulfill ROHS Guideline
- 5. ELECTRONIC TEST  
100% OPEN SHORT+MISS WIRE TEST

DRAWING

DB9PIN JACK(J1)	WIRE	DB9PIN JACK(J2)
2	—————	3
3	—————	2
4	—————	6
5	—————	5
6	—————	4
7	—————	8
8	—————	7
SHELL	DRAIN WIRE	SHELL

PART NO   4070-XX	SHEET NO   1	THIRD ANGLE PROJECTION
TITLE: DB9 PIN FEMALE TO DB9 PIN MALE BEIGE COLOR		
DWN NO   1219-05		SIZE   A4   CHECKED BY & DATE
		UNIT   mm   INCH   APPROVED BY & DATE