



Unique Selling Features

- Screw mounting from the back
- Power Switch illuminated or non-illuminated 2 pole 125/250VAC
- PCB Mounting
- Inrush current for switch up to 100A

Technical Details:

2 Pole Power Switch

Rated Voltage: 125/250VAC: 50/60Hz

Rated current: 10A for ENEC/VDE and UL/CSA

Pin temperature: 70°C

Operating temperature: -25°C bis +70°C

Panel Thickness: max: 3,5mm

Dielectric Strength: > 1.7 kVDC between L-N

> 2.7 kVDC zwischen L/N-PE

Degree of protection: IP40

Part number	Description
DC21.0021.1111	DC21 Screw mount, non- illuminated
DC21.0023.1111	DC21 Screw mount, illuminated red
DC21.0024.1111	DC21 Screw mount, illuminated green