

Catalogue Proposal Farnell 2008

DC22 Power Entry Module with filter
for PCB mounting



Unique Selling Feature

- Screw mounting from the back
- Power switch 2 pole, 125/250VAC
- Standard filter 2pole
- PCB mounting
- Space saving component

Technical details:

2 Pole Power Switch-non illuminated

Rated Voltage:125/250VAC: 50/60Hz
 Rated current: 1-10A for ENEC/VDE and UL/CSA
 Pin temperature: 70°C
 Operating temperature: -25°C to +85°C
 Panel Thickness: max: 4,0mm
 Dielectric Strength: > 1.7 kVDC between L-N
 > 2.7 kVDC zwischen L/N-PE
 Degree of protection: IP40

Typ	Description
DC22.1121.111	DC22 Screw mounting, non-illuminated-switch,1A
DC22.2121.111	DC22 Screw mounting, non-illuminated-switch,2A
DC22.4121.111	DC22 Screw mounting, non-illuminated-switch,4A
DC22.6121.111	DC22 Screw mounting, non-illuminated-switch,6A
DC22.9121.111	DC22 Screw mounting, non-illuminated-switch,10A