


CZ2

Handzange für das Anschlagen von Crimp-Anschlussfedern

1. Einsatzgebiet

Crimp-Anschlussfeder	3111 01 L, 3111 03 L, FC 01 L, FC 03 L
Lieferzustand	lose
Anschlagbare Leitung	Schaltlitze, Einzeldraht

2. Leistungsmerkmale

Anwendung	Labor- und Musterfertigung, Reparaturen
Anschlagleistung	ca. 200/h

3. Abmessungen

Abmessungen (H x B x T)	15 mm x 60 mm x 200 mm
Gewicht	ca. 0,3 kg

CZ2

Manual tongs for termination of crimp contact springs

1. Range of applications

Crimp contact spring	3111 01 L, 3111 03 L, FC 01 L, FC 03 L
State of delivery	in bulk
Processable conductor	stranded wire, single wire

2. Features

Application	laboratory and sample production, repair
Stroke capacity	ca 200/h

3. Dimensions

Dimensions (H x W x D)	15 mm x 60 mm x 200 mm
Weight	ca 0.3 kg

CZ2

Manual tongs for termination of crimp contact springs

1. Range of applications

Crimp contact spring	3111 01 L, 3111 03 L, FC 01 L, FC 03 L
State of delivery	in bulk
Processable conductor	stranded wire, single wire

2. Features

Application	laboratory and sample production, repair
Stroke capacity	ca 200/h

3. Dimensions

Dimensions (H x W x D)	15 mm x 60 mm x 200 mm
Weight	ca 0.3 kg