

Fully sealable Emily lenses for Osram Oslon SSL LEDs





- Specially designed for Osram Oslon SSL series of LEDs.
- Lens material optical grade PMMA with high UV and
- temperature resistance (105°C/220°F)
- High optical efficiency, up to 90%
- No lens holder. Lens has small position pins, fastening to heat sink with a PU foam adhesive tape of automotive grade. For mounting instruction, please see datasheet at the bottom page.
- Lens foot can be potted with resin without losses in optical efficiency (fully sealed construction of luminaire possible)
- Diameter 26 mm, height 15mm

LENS TYPES

NAME	ORDERING CODE	FWHM Angle
Emily Smooth Spot	CA11387_Emily-SS-OSL	Coming soon
Emily Medium	CA11388_Emily-M-OSL	Coming soon
Emily Oval	CA11389_Emily-O-OSL	Coming soon
Emily Oval 90°	CA11390_Emily-O-90-OSL	Coming soon

MEASUREMENTS


Coming soon

© Ledil Oy – Subject to change without prior notice



LEDIL F'FORM OPTICS

DRAWINGS



© Ledil Oy – Subject to change without prior notice