

Epson Stylus SX425W

FACTSHEET

Launch RRP inc VAT: £99.99

Launch date: 1st June 2010



Print and scan effortlessly from anywhere in the home with this wireless all-in-one. View and print using the LCD screen and make copies too. It's all very economical with individual ink cartridges.

- Lose the wires and bring Epson quality to family documents and photos from anywhere in the home with this wireless all-in-one
- Work at faster speeds and print at a longer range with the latest 802.11n wireless technology*2
- Print first-class documents and lab-quality photos with Epson DURABrite Ultra Ink
- Save money with individual inks – only replace the colour used. Choose from a range of ink cartridge sizes to meet your printing needs
- Epson DURABrite Ultra Ink delivers fast-drying prints that resist water, highlighter pens, smudging and fading
- View and print photos direct from memory card with the bright 3.8 cm LCD screen, making printing even more convenient
- Print text documents at up to 35 ppm*1 plus fast scanning and copying
- Power-efficient ENERGY STAR® qualified printer for reduced bills and environmental impact
- Includes Epson software to adjust colour and contrast, restore images, remove dust and correct backlight when you scan faded photos
- Includes ABBYY FineReader® OCR software, which scans text documents into editable files on your PC

EPSON DURABRITE ULTRA INK

Epson DURABrite Ultra Ink is perfect for all your home printing because it gives you long-lasting Epson quality on a wide range of media.













- First-class documents and lab-quality photos
- Instant-drying prints are water, smudge, highlighter and fade resistant
- Resin-coated pigment technology works perfectly on a range of papers
- Lab-quality glossy photos last over 200 years in a photo album*1



FOR THE BEST RESULTS ALWAYS USE GENUINE EPSON INK AND PAPER.

EPSON[®]
EXCEED YOUR VISION

INK CARTRIDGE COMPATIBILITY

| | BLACK | CYAN | MAGENTA | YELLOW | MULTIPACK |
|--|--|--|---|--|---|
|  <p>Wallet-friendly individual ink cartridges for less frequent printing</p> |  <p>● T1281</p> |  <p>● T1282</p> |  <p>● T1283</p> |  <p>● T1284</p> |  <p>●●●● T1285</p> |
|  <p>Print more pages at a low cost per page</p> |  <p>● T1291</p> |  <p>● T1292</p> |  <p>● T1293</p> |  <p>● T1294</p> |  <p>●●●● T1295</p> |

RECOMMENDED PAPER

The Epson Micro Piezo™ inkjet technology creates precise, perfectly formed ink droplets producing outstanding documents and photos on a wide range of media. Use Epson inks and paper for superb printing on everything from A4 inkjet paper to glossy photo paper in various sizes.



PHOTO PAPER



GLOSSY PHOTO PAPER



PREMIUM GLOSSY PHOTO PAPER



RECOMMENDED SYSTEM REQUIREMENTS

| DESCRIPTION | PROCESSOR | RAM | HARD DISK SPACE |
|---|-----------|-------|-----------------|
| Microsoft® Windows® XP | 1GHz | 512MB | 1GB |
| Microsoft® Windows® XP Professional x64 Edition | *3 | *3 | 1GB |
| Microsoft® Windows Vista® | *3 | *3 | 1GB |
| Microsoft® Windows®7 | *3 | *3 | 1GB |
| Mac OS® X 10.4,11 or later*4*5 | *3 | *3 | 1GB |

WHAT'S IN THE BOX

- Epson Stylus SX420W series printer
- 4 individual ink cartridges
- Software CD
- Basic operation guide
- 'Start Here' guide
- Wi-Fi/Network set-up guide
- Control panel icon sticker
- Warranty document
- Power cable

CONNECTIVITY

| | | |
|--------------|-----------------|--------------|
| 802.11 b/g/n | ETHERNET 10/100 | HI-SPEED USB |
| • | - | • |

PRODUCT SPECIFICATIONS

| | | | | | | | | | | | | | |
|---|---|---------|--------|---------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| PRINT TECHNOLOGY Printing method Nozzle configuration Droplet size Ink system | 4-colour inkjet printer, Epson Micro Piezo™ print head 128 nozzles black / 42 nozzles for each colour (cyan, magenta, yellow) 3 pl (minimum) with Variable-sized Droplet Technology Epson DURABrite Ultra Ink | | | | | | | | | | | | |
| PRINT RESOLUTION | Up to 5760x1440 optimised dpi on suitable media using RPM (Resolution Performance Management) | | | | | | | | | | | | |
| PRINT SPEED Black text A4 Colour text A4 Photo 10x15 cm | Up to 35 ppm*1 Up to 15 ppm*1 Approx. 54 secs*1 | | | | | | | | | | | | |
| SCANNING Scan resolution Technology Sensor type Speed | 1200x2400 dpi A4 flatbed colour image scanner CIS Black A4: 300 dpi 2.2 msec/line, 600 dpi 7.2 msec/line Colour A4: 300 dpi 7.2 msec/line, 600 dpi 13.1 msec/line | | | | | | | | | | | | |
| LCD AND MEMORY CARDS LCD screen Supported memory cards | 3.8 cm colour Memory Stick, Memory Stick Duo®6, MagicGate Memory Stick, MagicGate Memory Stick Duo®6, Memory Stick PRO, Memory Stick PRO Duo®6, SD, SDHC, MiniSD®6, MiniSDHC®6, MicroSD®6, MicroSDHC®6, Multi Media Card, MMCplus, MMCmobile®6, MMCmicro®6, xD-Picture card, xD-Picture card Type-M, xD-Picture card Type-M+, xD-Picture card Type-H | | | | | | | | | | | | |
| INTERFACE USB Wi-Fi | Hi-Speed USB – compatible with the USB 2.0 specification Wireless LAN IEEE 802.11b/g/n | | | | | | | | | | | | |
| WIRELESS SECURITY | WEP – 64bit WEP – 128 bit WPA – PSK (TKIP) – compliant with WPA2 WPA – PSK (AES) – compliant with WPA2 | | | | | | | | | | | | |
| PAPER HANDLING Capacity Media size Print margin | Input: 120 sheets A4 plain paper (64 g/m²) or 20 sheets Premium Glossy Photo Paper A4, Letter, Legal, 20x25 cm, 13x20 cm, 13x18 cm, 10x15 cm, 9x13 cm, A5, A6, B5, 16:9 wide size, User Defined, Envelopes: No.10, DL, C6 0 mm top, left, right, bottom via custom settings in printer driver*7 | | | | | | | | | | | | |
| INK CARTRIDGES Fox series Apple series | 4 individual ink cartridges <table border="1"> <tr> <td>Black</td> <td>Cyan</td> <td>Magenta</td> <td>Yellow</td> </tr> <tr> <td>T1281</td> <td>T1282</td> <td>T1283</td> <td>T1284</td> </tr> <tr> <td>T1291</td> <td>T1292</td> <td>T1293</td> <td>T1294</td> </tr> </table> | Black | Cyan | Magenta | Yellow | T1281 | T1282 | T1283 | T1284 | T1291 | T1292 | T1293 | T1294 |
| Black | Cyan | Magenta | Yellow | | | | | | | | | | |
| T1281 | T1282 | T1283 | T1284 | | | | | | | | | | |
| T1291 | T1292 | T1293 | T1294 | | | | | | | | | | |
| ELECTRICAL SPECIFICATION Power consumption Voltage | Approx. 13W (standalone copying, ISO/IEC24712 Letter) Approx. 4.0W (sleep mode) ENERGY STAR® qualified all-in-one AC 220-240V | | | | | | | | | | | | |
| OPERATING SYSTEMS | Windows XP/XP-x64/Vista, Win 7, Mac OS 10.4.11 or later | | | | | | | | | | | | |
| WARRANTY | 1 year standard warranty Optional extension to 3 years subject to availability | | | | | | | | | | | | |
| GENERAL Dimensions (WxDxH) including carton box Weight Dimensions (WxDxH) excluding carton box Weight Noise level | 516x230x398 mm 7.5 kg 450x342x182 mm 5.7 kg (excluding ink cartridges and power cable) 5.3 B(A) (according to ISO7779 pattern with Epson Premium Glossy Photo Paper/Photo RPM mode) 38 dB(A) (according to ISO9296) | | | | | | | | | | | | |
| SOFTWARE | Epson Easy Photo Print Epson Event Manager EpsonNet Setup Epson Web Support ABBYY FineReader® 9.0 Sprint (PC) ABBYY FineReader® 8.0 Sprint (Mac) | | | | | | | | | | | | |

PRODUCT LOGISTICS INFORMATION

| DESCRIPTION | PALLET QUANTITY | COUNTRY OF ORIGIN | SKU DESCRIPTION | SKU CODE | EAN BARCODE |
|---|---|-------------------|-----------------|------------|---------------|
| Epson Stylus SX425W | 45 | Indonesia | EUL | C11CA80311 | 8715946466873 |
| PRODUCT DETAILS | | | | | |
| Dimensions (WxDxH) | 450x342x182 mm | | | | |
| Weight | 5.7 kg (excluding ink cartridges and power cable) | | | | |
| PACKAGE SPECIFICATIONS | | | | | |
| Dimensions (WxDxH) | 516x230x398 mm | | | | |
| Weight | 7.5 kg | | | | |
| WARRANTY | | | | | |
| 1 year standard warranty. Optional extension to 3 years subject to availability | | | | | |

OTHER PRODUCTS WITHIN THIS RANGE

Lose the wires and make Epson quality home printing easy with these stylish all-in-ones with Wi-Fi and money-saving individual inks.

Epson Stylus SX425W

£99.99



- Effortless all-in-one with Wi-Fi
- Fast printing, scanning and copying
- LCD screen to quickly view and print photos
- Choice of cartridge capacities to meet your printing needs
- Save money with individual ink cartridges

[For more information click here](#)

Epson Stylus SX525WD

£149.99



- Fast, sleek wireless home all-in-one with LCD screen
- Auto double-sided printing
- Superb, long-lasting Epson quality
- Choose large or extra large capacity cartridges to suit your printing needs

[For more information click here](#)

Epson Stylus SX620FW

£199.99



- The complete wireless home 4-in-1
- Auto document feeder for multiple-page documents
- Superb, long-lasting Epson quality
- Choose large or extra large capacity cartridges to suit your printing needs

[For more information click here](#)

Epson Stylus Photo PX710W

£199.99



- Stylish, wireless all-in-one
- Print better-than-lab-quality photos
- A4 and photo front-loading paper trays
- Print directly onto suitable CDs/DVDs

[For more information click here](#)

Epson Stylus Photo PX810FW

£299.99



- Elegant, wireless 4-in-1 with touchscreen panel
- Print better-than-lab-quality photos
- Auto document feeder for multiple-page documents
- Auto double-sided printing

[For more information click here](#)



*1 For more information please visit www.epson-europe.com *2 When used with other 802.11n products. Wi-Fi speed may vary depending on physical environment *3 Refer to OS recommended system requirements *4 Some applications and/or functions may not be supported under Mac OS® X *5 Utility software support provided by Apple's Rosetta for Intel-based Macs *6 Adaptor required (not supplied in box) *7 Otherwise 3 mm top, left, right, bottom

For more information please contact

Telephone: 0871 222 6702 (UK)*
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

* Calls cost 10 pence per minute from a standard BT landline.
Calls from other networks and mobiles may vary.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.