

IDXPERT™ Handheld Labeler



More Options, More Brains, More Brawn...Less Waste.

More Types of Labels

- Colored Continuous tapes for equipment ID and safety warnings
- PermaSleeve™ wire marker sleeves
- Self-Laminating wire & cable markers
- Terminal Block markers
- Patch Panel markers
- Face Plate & Outlet markers
- General-purpose industrial die-cut labels

More Sizes

- Prints from .06" up to 1.25" characters on label stock up to 1.5" wide

More Symbols

- Code 39 and 128 bar codes
- 82 Symbols including electrical, voice/data, safety & protection, warning, and machine & operational

More Brains

- Drop Lock & Go™ Smart Cartridges™ are fast to install and remove
- Electronically pre-calibrated to orient the label just the way you need it with no special keys to press
- Print stand-alone or from a PC (with optional Brady LabelMark™ software)
- Memory to store frequently used set-ups

Prints Clean & Fast

- Users of dot-matrix printers will benefit from crisp, non-smearing thermal transfer print quality, faster print speed and more text-editing and symbols capabilities

Less Waste

- Edge-to-edge printing on continuous tapes so you don't pay for unused label material
- Die-cut labels are pre-cut to the size you need—no waste
- Runs on 6 AAs or optional AC power supply




Two printer layouts—identical functionality and supplies.

Catalog No.	Description
XPERT-ABC	Printer*(ABC Layout)
XPERT-HC-ABC	Hard Case for ABC Layout
XPERT-KEY	Printer*(KEYBOARD Layout)
XPERT-HC-KEY	Hard Case for KEYBOARD Layout
XPERT-AC	AC Adapter
LABXPRT-SER-USB	Serial-to-USB adapter for PC cable
PCCABLE-1	Spare PC Cable for Upgrades Only
PCK-6	Cleaning Kit
LM3	LabelMark™ software (single user)

*Printer ships with: Hard Case, 1.5" Cont. Tape, PC cable Product CD

Diagram



Indoor/Outdoor Grade Facility & Safety Labels

This indoor/5 year outdoor vinyl is very pliable and conforms well to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins and equipment. Aggressive permanent adhesive. Excellent resistance to oils, detergents, dirt, grime and many solvents.

- B-580 Indoor/Outdoor Vinyl material
- Permanent adhesive, good for rough surfaces
- Temp Range -40°F to 248°F (-40C to 120C)

Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color
			A	B	A	B	
⊙	XC-500-580-WT-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	BK on WT
⊙	XC-1000-580-WT-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	BK on WT
⊙	XC-1500-580-WT-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	BK on WT
⊙	XC-500-580-OR-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	BK on OR
⊙	XC-1000-580-OR-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	BK on OR
⊙	XC-1500-580-OR-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	BK on OR
⊙	XC-500-580-YL-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	BK on YL
⊙	XC-1000-580-YL-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	BK on YL
⊙	XC-1500-580-YL-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	BK on YL
⊙	XC-500-580-CL-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	BK on CL
⊙	XC-1000-580-CL-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	BK on CL
⊙	XC-1500-580-CL-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	BK on CL
⊙	XC-500-580-RD-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	WT on RD
⊙	XC-1000-580-RD-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	WT on RD
⊙	XC-1500-580-RD-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	WT on RD
⊙	XC-500-580-GN-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	WT on GN
⊙	XC-1000-580-GN-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	WT on GN
⊙	XC-1500-580-GN-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	WT on GN
⊙	XC-500-580-BL-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	WT on BL
⊙	XC-1000-580-BL-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	WT on BL
⊙	XC-1500-580-BL-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	WT on BL
⊙	XC-500-580-WT-RD	1 roll (cont.)	30 ft.	0.500	9.14m	12.70m	RD on WT
⊙	XC-1000-580-WT-RD	1 roll (cont.)	30 ft.	1.000	9.14m	25.40m	RD on WT
⊙	XC-1500-580-WT-RD	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	RD on WT