



90325- * **

n TIN ASSY
 m GOLD ASSY
 STANDARD VOIDED OPTION SEE SHEET
 D PEG WITH KINKS OPTION SEE SHEET
 m GOLD, TUBED
 n TIN ASSY TUBED

G MATL. POLYESTER PBT 15% GLASS FILLED TO UL94 V-0.
 ATL. BRASS (0.28)/.011 THK
 ING. TIN: (1.27um)/50u" MIN NICKEL
 \ - III / I - I" TI
 ING. GOLD: (1.27um)/50u" MIN. NICKEL
 \ - III / I - I" TI SELECTIVE
 (0.76um)/30u" - - TI - GOLD
 RMS TO PRODUCT SPECIFICATION PS-99020-0011

ADD CKT.1 INDICATOR

	/I	/I	I
	I/I	/I	I
	/II	I /I	I
	/I	/II	I
	I /	I /I	I
	/	/	
	II /	/	
	I /	I /	2
	I /	I /	
	/	II /	
	I /	/	
	I	I	I T I

