


SEE CHART
SD-92315-001



90327 CONNECTOR	
CIRCUIT SIZE	DIMENSION W
4	7.59
6	10.13
8	12.67
10	15.21
12	17.75
14	20.29
16	22.83
18	25.37
20	27.91
22	30.45

CABLE DETAILS:

28 AWG , 1.27 MM PITCH , 7 STRANDS WITH TINNED COPPER ,
GREY PVC INSULATION WITH A COLOURED POLARITY STRIPE
INDICATING CIRCUIT NO. 1 , UL 2651.

NOTES:

1. SEE PRODUCT SPECIFICATIONS PS-99020-0011.
2. SEE TERMINATION SPECIFICATION ES-99033-0001.
3. SEE CABLE SPECIFICATION ES-99027-0006.
4. HARNESSES WILL BE 100% ELECTRICALLY TESTED FOR SHORTS AND DISCONTINUITIES.

ORDERING INFORMATION

92315-****

CIRCUIT SIZE
LENGTH L IN CENTIMETRES

LENGTHS AVAILABLE FROM 6 CM TO 120 CM

e.g. 92315-1208 = 12 CIRCUIT
WITH LENGTH L OF 8 CM.

NOTE : FOR LENGTHS OF

- 100 CM , THE PART NO. IS 92315-***01
- 105 CM , THE PART NO. IS 92315-***02
- 110 CM , THE PART NO. IS 92315-***03
- 115 CM , THE PART NO. IS 92315-***04
- 120 CM , THE PART NO. IS 92315-***05

ADDED OPTION
2002-1088
MKUBOVCI020607
//
//
//

4 : 1 x

MCURRAN 98/06/19

AMcCANN 98/06/19

MWILHITE 98/06/19

PICOFLEX IDT TO IDT
STANDARD ASSEMBLIES

1/2

S92315X1.DGN SEE CHART SD-92315-001