



PMS 2600

Industrial Connectors:Measuring and Testing Equipment:Sets/Accessories:4 mm safety system

Product description

Description Test equipment set for safety applications, as accessories for measuring instruments.
 2 x Clamp-type test probe KLEPS 2600
 2 x Test-Probe PRUEF 2600
 2 x Crocodile clip AK 2 B
 2 x Safety test lead MLS GG 100/1

Type PMS 2600
 Order No. 972 338-001
 System 4 mm safety system
 Cable length 100 cm
 Conductor size 1 mm²
 Cable material PVC
 Cable color Each article in black and red.
 Housing Color Each article in black and red.
 Clamping range 4 mm - 9,5 mm

Technical data

Pin dimensions 4 mm
 Type of contact socket, pin (spring-loaded)
 Type of termination 4 mm diameter pin and socket
 Standard IEC 61010
 Cable type LEH-XY
 Cable specification highly flexible lead
 Wire stranding 259 x 0,07
 Rated voltage AC/DC 1000 V; AK 2 B: AC/DC 300 V
 Measurement Category CAT III; AK 2 B: CAT II

Environmental conditions

Temperature range -15 °C to +70 °C