

2 Port USB DVI Cable KVM Switch with Audio

StarTech ID: SV215MICDVIA



This USB DVI Cable KVM Switch supports superior video quality (resolutions up to 1920x1200), offering a high resolution solution for accessing and controlling two desktop computers from a single KVM (Keyboard, Video, Mouse) peripheral set.

A complete KVM solution, this cable-style KVM switch includes all of the cables and connections required to share one DVI monitor, keyboard and mouse, as well as speakers, across two computers. Plus, the switch features independent audio/microphone switching to ensure an uninterrupted audio experience, even when switching between computers.

This broadly compatible USB KVM switch can be connected to Mac, Linux or PC-based computers, making it a convenient solution for most operating environments. Plus, because of its space-saving “KVM-on-a-cable” design, no desk space is required for installation – an ideal choice for most applications, including SOHO (small or home offices), gaming, multimedia production workstations and more.

Applications and Solutions

- Ideal for desktops, workstations and servers that require full multi-media support.
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required.
- Sharing computers and attached peripherals in the home/SOHO/multimedia environment

Features

- Compatible with all USB supported Operating Systems.
- Complete micro design saves space and money
- Computer selection by Remote selector and keyboard hotkeys
- Designed for high-resolution applications: 1920 x 1200 analog resolution with DDC2B
- HDCP Compliant
- Hot Pluggable - add or remove computers without having to power down the computers.
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Humidity: 0~80% RH,
- Operating Temperature: 0°C to 50°C (32°F to 122°F)
- Carton Quantity: 10
- Storage Temperature: -20°C to 60°C (-4°F to 140°F)
- Shipping (Package) Weight: 1.59 lb [0.72 kg]
- Enclosure Type: Plastic
- Audio Support: Yes
- KVM Cascadable: No
- Supported Platforms: USB
- Rack-Mountable: No
- Maximum Number of Users: 1
- Number of KVM Ports: 2
- Connectors:
 - Host : 2 x DVI-D Single Link Male
 - 4 x USB A Male
 - 4 x Stereo 3.5mm Audio Male
 - Console : 1 x DVI-D Single Link Female
 - 2 x USB A Female
 - 2 x Stereo 3.5mm Audio Female

- **Note:** One host cable is 47 inches long, the other is 24 inches
- Remote selector is 70 inches long

