

Epson Perfection V330 Photo

Epson Perfection V330 Photo



Superior quality, expert scanning for photos, slides and film

Capture more detail with this 4800 dpi Charged Coupled Device (CCD) scanner that has the superior quality you'd expect from an Epson Perfection scanner. With virtually no warm-up time and low power consumption, Epson ReadyScan LED technology offers expert scanning for photos. The built-in transparency unit can be opened in either portrait or landscape orientation for convenient scanning of slides and film, and even bulky or 3D objects. The included stitching software*¹ allows you to scan materials larger than A4 and a dedicated button lets you scan to multi-page, searchable PDF, or scan straight to email. Epson Easy Photo Fix™ software makes it simple to restore colour, remove dust and correct backlight for perfect results.

- Low power consumption thanks to ReadyScan LED technology
- Scan film and slides with built-in transparency unit
- Scan larger than A4 with included stitching software (software compatible with Microsoft Windows only)
- Capture more detail from film and slides with 4800 dpi optical resolution CDD
- Get superior scan quality with virtually no warm-up time
- Restore colour, remove dust and correct backlight with included Epson Easy Photo Fix™ software
- Scan straight to email with one-touch button
- Scan to multi-page, searchable PDF
- Scan in portrait or landscape
- Scan books and 3D objects with extendable hinge design

WHAT'S IN THE BOX

- Epson Perfection V330 Photo Scanner
- Film holder
- Software CD-ROM
- 'Start Here' guide
- AC Adapter
- Warranty document
- USB cable

SCANNER TYPE Optical resolution Optical density Document size Interface	Flatbed colour image scanner Main 4800 dpi x Sub 9600 dpi 3.2 Dmax Flatbed A4, US letter size document, TPU - 35 mm x6 frames (strip film), 35 mm x4 frames (slide film) USB 2.0 Hi-speed
CONFIGURATION Photo-electric device Light source Sub-scanning method	12 line colour Epson Matrix CCD™ with on chip Micro Lens White LED Fixed documents and moving carriage
PERFORMANCE Output resolution	50-6400, 9600, 12800 dpi Internal 48-bit colour (281.5 trillion colours) Output 48-bit colour (281.5 trillion colours) 24-bit (16.7 million colours) 16-bit (65,536 gray scale levels) 8-bit (256 gray scale levels) 1-bit (monochrome)
FUNCTIONS Image quality enhancer Easy scanning	Print Image Matching-II-Image enhancement function: Backlight Correction, dust removal for film, colour restoration, grain reduction, selectable tone of auto-exposure, unsharp mask with noise reduction, de-screening with document type optimizer, tone curve adjustment with histogram 4 Easy Push Buttons linked to Epson Event Manager, Stitching software ¹ , Multiple page scan to PDF with scanner buttons, High compression PDF, Search PDF, Text Enhancement, Color Enhance and Drop-out features, Correct Document Skew, stand-alone application and scan to file feature, multi-purpose user interface, multi-document auto detection, auto photo orientation, multi-document auto cropping, auto skew correction, multi-marquee, film scanning thumbnail preview
SCANNING SPEED Reflective scanning Film and transparencies	A4 preview: 7 seconds A4 line art 600 dpi: 25 seconds A4 colour 600 dpi: 29 seconds A4 colour 1200 dpi: 102 seconds Single frame 35 mm positive film 4800 dpi (best/draft): 86/63 seconds Single frame 35 mm negative colour film 4800 dpi (best/draft): 118/87 seconds
ENVIRONMENTAL CONDITIONS Temperature Humidity	5°C to 35°C (operating) 10% to 80% without condensation (operating)
OPTIONS Warranty ²	1 year standard. Optional extension to 3 years, subject to availability
ELECTRICAL SPECIFICATIONS Voltage Power consumption	AC 200-240V, 50-60Hz 12 Watts operating, 3.7 Watts in sleep mode
GENERAL Dimensions (WxDxH) Weight	430x280x66.5 mm Approx. 2.8 kg
OPERATING SYSTEMS	Windows® XP / XP-x64 / Vista® / Win 7 / Mac OS® X 10.3.9 or later
SOFTWARE	Epson Scan, Epson Event Manager, Arcsoft Scan-n-Stitch™ Deluxe ¹ , ArcSoft MediaImpression®, ABBYY FineReader® 9 Sprint Plus (PC), ABBYY FineReader® 8 Sprint Plus (Mac)

¹ Supplied stitching software compatible with Microsoft Windows only.

² Warranty offers are not available for all countries. Please contact your local Epson representative.



Better Products for a Better Future

For more information please contact

Telephone: 0871 222 6702 (UK)*
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

* Calls cost 10 pence per minute from a standard BT landline.
Calls from other networks and mobiles may vary.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.