


NOTE:

1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm (REF)

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	9/10/96	<i>D. Camello</i>
B	REVISED PER ECN 0020-0262-01	G.V. 12/18/02	JGH



HOUSING MOUNTING NUT LOCKWASHER	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35	
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A	
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	
O-RING	FLOUROSILICONE PER MIL-R- 25988, CLASS I, TYPE I.	N/A	
COMPONENT	MATERIAL	FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY K.LE DATE 9-10-96	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	
FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1°	CHECKED BY APP'D BY <i>D. Camello</i> 9/10/96		
These drawings and specifications are the property of M/A CDM Interconnect Div. and shall not be reproduced or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE OSP JACK TO DSP BULKHEAD FEEDTHROUGH PLUG ADAPTER	
	NO. A.P. N/A	SIZE B	CODE IDENT NO. 26805
		SCALE 5:1	4585-2240-02
		N/A	SHEET 1 OF 1

CUSTOMER DRAWING

AMP PART # 1059756-1
SHEET 1 OF 1 REV B