1-800-383-7323 USA/CAN www.energizer.com

## **EVEREADY 711**



## **Industry Standard Dimensions**

Chemical System: Zinc-Manganese Dioxide (Zn/Mn02)

Designation: ANSI / NEDA-700, IEC-R25-2

Battery Voltage: 1.5 Volts

Average Weight: 300 grams (10.6 oz.)


**Volume:** 334 cubic centimeters (12.4 cubic inch)

Average Capacity: 2,200 mAh to 0.8 volts/cell

(Rated at 25 mA continuous drain at 21°C)

Cells: Two No. 60 (size "F") in parallel

Jacket: Paper



## Simulated Application Test Estimated Average Service at 21°C (70°F)

	Typical Drains at 1.2V (milliamperes)	Load (ohms)	Cutoff Voltage		
Schedule:			0.8V	0.9V 1.0V	1.1V
			Hours		
4 hours/day	240	5		78 61	54
5 min/20 min 8 hours/day	910	1.32	17	15 13	10

## **Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. Inc. - All Rights Reserved

Form No. EBC - 3230D Page 1 of 1