

38090101



Wiha. Premium Werkzeuge für Profis.



- Blade High grade chrome-vanadium steel, through hardened.
- Handle Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
- Bit holder Stainless steel with strong magnet.
- Suitable for DIN 3126, ISO 1173, style D 6.3.
- Bits 25 mm Standard bits.
- Application The alternative to a screwdriver set.

Order No.	⌀	⇄	⊕	⊖	⊕	⊗
01626	6,5	25		1,2		
01657		25	PH1			
01658		25	PH2			
01659		25	PH3			
01689		25			PZ2	
01717		25				T15
01718		25				T20
01719		25				T25



Wiha. Premium Werkzeuge
für Profis.

38090201

Insulation up to 1000 V AC.



- Blade High grade chrome-vanadium steel, through hardened.
Insulation moulded directly onto blade.
- Handle Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
- Bit holder Stainless steel with strong magnet.
- Suitable for DIN 3126, ISO 1173, style D 6.3.
- Standards Routine test based on IEC 60900:2004.
- Bits 25 mm Standard bits.
- Application The alternative to a screwdriver set.

Order No.	⌀	⇄	⊕	⊗	⊖
01626	6,5	25			1,2
01623	4,5	25			0,6
01657		25	PH1		
01688		25		PZ1	
01658		25	PH2		
01659		25	PH3		
01689		25		PZ2	
01690		25		PZ3	