



$\frac{7}{16}$  - 28 UNF - 2B THREAD

STAMP: KINGS KA-59-69

- NOTES:**
1. FOR USE WITH RG-174, 179, 187 & 188/U CABLES.
  2. FOR CABLE TRIMMING USE KTJ-30.
  3. FOR CRIMPING USE DIE SIZE 32.
  4. FOR CABLING INSTRUCTIONS SEE CP-406.

**UNLESS OTHERWISE SPECIFIED:**

- |   |  |
|---|--|
| 1. TOLERANCES:<br>FRACTIONS & .010 DECIMALS ± .004 ANGLES ± 0° 30'                    | 2. REMOVE ALL BURRS, BREAK SHARP EDGES .003 MAX. |
| T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED THE SUM OF THEIR TOLERANCES. | 3. NO FILLETS PERMITTED.                         |
|   | 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.     |
|   | 5. ALL DIMENSIONS PRIOR TO PLATING.              |

ITEM	REQ'D	DESCRIPTION	DWG. NO.
9	1	INSULATOR	
8	1	TNC CAPTIVE CONTACT M-F	
7	1	COUPLING NUT	
6	1	GASKET	
5	1	CRIMP CONTACT	C-59-95-2-M07
4	1	C-RING	
3	1	INSULATOR	
2	1	BODY ASSEMBLY	
1	1	K-GRIP SLEEVE	S-89-67-2-MC7

KA-59-69

REVISIONS	
NO.	CHANGES
1	CN 6350 A 19 AUG 68 ANE
2	CN 11107 A J.G.L. 25 APR 72
3	CN 25062 C JEP 1 SEPT 83

REF.	
FINISH	
SPEC.	KER 10004
MATL.	
SPEC.	
<b>TNC PLUG</b>	
DRAWN	A. T. DATE 8 FEB 66
APPR.	L. I. DATE 9 FEB 66
<b>KINGS ELECTRONICS</b> 40 MARLBOROUGH ROAD TUCKAHOE, N. Y.	
<b>KA-59-69</b>	