

TK Polystyrene

- Flame-resistant
- Impact-resistant
- Temperature-resistant to 70°C



| Base grey lid grey | | | | | | | |
|-------------------------------------|------------|---------------------------------|------------|----------------------|------------|-----------------|--|
| with Pg knockouts | | with metric knockouts | | with smooth walls | | | |
| Type | Order N° | Type | Order N° | Type | Order N° | Dimensions | |
| PS 77 - 6 | 115 401 01 | PS 77 - 6-m | 105 401 01 | PS 77 - 6-o | 110 401 01 | 65 x 65 x 57 | |
| PS 77 - 8 | 115 901 01 | PS 77 - 8-m | 105 901 01 | PS 77 - 8-o | 110 901 01 | 65 x 65 x 81 | |
| PS 97 - 6 | 115 402 01 | PS 97 - 6-m | 105 402 01 | PS 97 - 6-o | 110 402 01 | 94 x 65 x 57 | |
| PS 97 - 8 | 115 902 01 | PS 97 - 8-m | 105 902 01 | PS 97 - 8-o | 110 902 01 | 94 x 65 x 81 | |
| PS 99 - 6 | 115 403 01 | PS 99 - 6-m | 105 403 01 | PS 99 - 6-o | 110 403 01 | 94 x 94 x 57 | |
| PS 99 - 8 | 115 903 01 | PS 99 - 8-m | 105 903 01 | PS 99 - 8-o | 110 903 01 | 94 x 94 x 81 | |
| PS 1111 - 7 | 115 404 01 | PS 1111 - 7-m | 105 404 01 | PS 1111 - 7-o | 110 404 01 | 110x 110 x 66 | |
| PS 1111 - 9 | 115 904 01 | PS 1111 - 9-m | 105 904 01 | PS 1111 - 9-o | 110 904 01 | 110x 110 x 90 | |
| PS 1309 - 6 | 115 409 01 | PS 1309 - 6-m | 105 409 01 | PS 1309 - 6-o | 110 409 01 | 130 x 94 x 57 | |
| PS 1309 - 8 | 115 909 01 | PS 1309 - 8-m | 105 909 01 | PS 1309 - 8-o | 110 909 01 | 130 x 94 x 81 | |
| PS 1313 - 7 | 115 405 01 | PS 1313 - 7-m | 105 405 01 | PS 1313 - 7-o | 110 405 01 | 130 x 130 x 75 | |
| PS 1313 -10 | 115 905 01 | PS 1313 -10-m | 105 905 01 | PS 1313 -10-o | 110 905 01 | 130 x 130 x 99 | |
| PS 1809 - 6 | 115 410 01 | PS 1809 - 6-m | 105 410 01 | PS 1809 - 6-o | 110 410 01 | 180 x 94 x 57 | |
| PS 1809 - 8 | 115 910 01 | PS 1809 - 8-m | 105 910 01 | PS 1809 - 8-o | 110 910 01 | 180 x 94 x 81 | |
| PS 1811 - 9 | 115 406 01 | PS 1811 - 9-m | 105 406 01 | PS 1811 - 9-o | 110 406 01 | 180 x 110 x 90 | |
| PS 1811 -11 | 115 906 01 | PS 1811 -11-m | 105 906 01 | PS 1811 -11-o | 110 906 01 | 180 x 110 x 111 | |
| PS 1811 -16 | 114 406 01 | PS 1811 -16-m | 104 406 01 | PS 1811 -16-o | 109 406 01 | 180 x 110 x 165 | |
| PS 1818 - 9 | 115 407 01 | PS 1818 - 9-m | 105 407 01 | PS 1818 - 9-o | 110 407 01 | 182 x 180 x 90 | |
| PS 1818 -11 | 115 907 01 | PS 1818 -11-m | 105 907 01 | PS 1818 -11-o | 110 907 01 | 182 x 180 x 111 | |
| PS 1818 -16 | 114 407 01 | PS 1818 -16-m | 104 407 01 | PS 1818 -16-o | 109 407 01 | 182 x 180 x 165 | |
| PS 1818 -21 | 114 907 01 | PS 1818 -21-m | 104 907 01 | PS 1818 -21-o | 109 907 01 | 182 x 180 x 215 | |
| PS 2518 - 9 | 115 408 01 | PS 2518 - 9-m | 105 408 01 | PS 2518 - 9-o | 110 408 01 | 254 x 180 x 90 | |
| PS 2518 -11 | 115 908 01 | PS 2518 -11-m | 105 908 01 | PS 2518 -11-o | 110 908 01 | 254 x 180 x 111 | |
| PS 2518 -16 | 114 408 01 | PS 2518 -16-m | 104 408 01 | PS 2518 -16-o | 109 408 01 | 254 x 180 x 165 | |
| PS 2518 -21 | 114 908 01 | PS 2518 -21-m | 104 908 01 | PS 2518 -21-o | 109 908 01 | 254 x 180 x 215 | |
| PS 3625 -11 | 115 412 01 | PS 3625 -11-m | 105 412 01 | PS 3625 -11-o | 110 412 01 | 360 x 254 x 111 | |
| PS 3625 -16 | 115 912 01 | PS 3625 -16-m | 105 912 01 | PS 3625 -16-o | 110 912 01 | 360 x 254 x 165 | |
| PS 3625 -21 | 114 412 01 | PS 3625 -21-m | 104 412 01 | PS 3625 -21-o | 109 412 01 | 360 x 254 x 215 | |



| Base grey lid transparent | | | | | | |
|--|------------|---------------------------------|------------|----------------------|------------|-----------------|
| with Pg knockouts | | with metric knockouts | | with smooth walls | | |
| Type | Order N° | Type | Order N° | Type | Order N° | Dimensions |
| PS 77- 6-t | 116 001 01 | PS 77- 6-tm | 106 001 01 | PS 77- 6-to | 111 001 01 | 65 x 65 x 57 |
| PS 77- 8-t | 116 501 01 | PS 77- 8-tm | 106 501 01 | PS 77- 8-to | 111 501 01 | 65 x 65 x 81 |
| PS 97- 6-t | 116 002 01 | PS 97- 6-tm | 106 002 01 | PS 97- 6-to | 111 002 01 | 94 x 65 x 57 |
| PS 97- 8-t | 116 502 01 | PS 97- 8-tm | 106 502 01 | PS 97- 8-to | 111 502 01 | 94 x 65 x 81 |
| PS 99- 6-t | 116 003 01 | PS 99- 6-tm | 106 003 01 | PS 99- 6-to | 111 003 01 | 94 x 94 x 57 |
| PS 99- 8-t | 116 503 01 | PS 99- 8-tm | 106 503 01 | PS 99- 8-to | 111 503 01 | 94 x 94 x 81 |
| PS 1111 - 7-t | 116 004 01 | PS 1111 - 7-tm | 106 004 01 | PS 1111 - 7-to | 111 004 01 | 110x 110 x 66 |
| PS 1111 - 9-t | 116 504 01 | PS 1111 - 9-tm | 106 504 01 | PS 1111 - 9-to | 111 504 01 | 110x 110 x 90 |
| PS 1309 - 6-t | 116 009 01 | PS 1309 - 6-tm | 106 009 01 | PS 1309 - 6-to | 111 009 01 | 130 x 94 x 57 |
| PS 1309 - 8-t | 116 509 01 | PS 1309 - 8-tm | 106 509 01 | PS 1309 - 8-to | 111 509 01 | 130 x 94 x 81 |
| PS 1313 - 7-t | 116 005 01 | PS 1313 - 7-tm | 106 005 01 | PS 1313 - 7-to | 111 005 01 | 130 x 130 x 75 |
| PS 1313 -10-t | 116 505 01 | PS 1313 -10-tm | 106 505 01 | PS 1313 -10-to | 111 505 01 | 130 x 130 x 99 |
| PS 1809 - 6-t | 116 010 01 | PS 1809 - 6-tm | 106 010 01 | PS 1809 - 6-to | 111 010 01 | 180 x 94 x 57 |
| PS 1809 - 8-t | 116 510 01 | PS 1809 - 8-tm | 106 510 01 | PS 1809 - 8-to | 111 510 01 | 180 x 94 x 81 |
| PS 1811 - 9-t | 116 006 01 | PS 1811 - 9-tm | 106 006 01 | PS 1811 - 9-to | 111 006 01 | 180 x 110 x 90 |
| PS 1811 -11-t | 116 506 01 | PS 1811 -11-tm | 106 506 01 | PS 1811 -11-to | 111 506 01 | 180 x 110 x 111 |
| PS 1811 -16-t | 117 006 01 | PS 1811 -16-tm | 107 006 01 | PS 1811 -16-to | 112 006 01 | 180 x 110 x 165 |
| PS 1818 - 9-t | 116 007 01 | PS 1818 - 9-tm | 106 007 01 | PS 1818 - 9-to | 111 007 01 | 182 x 180 x 90 |
| PS 1818 -11-t | 116 507 01 | PS 1818 -11-tm | 106 507 01 | PS 1818 -11-to | 111 507 01 | 182 x 180 x 111 |
| PS 1818 -16-t | 117 007 01 | PS 1818 -16-tm | 107 007 01 | PS 1818 -16-to | 112 007 01 | 182 x 180 x 165 |
| PS 1818 -21-t | 117 507 01 | PS 1818 -21-tm | 107 507 01 | PS 1818 -21-to | 112 507 01 | 182 x 180 x 215 |
| PS 2518 - 9-t | 116 008 01 | PS 2518 - 9-tm | 106 008 01 | PS 2518 - 9-to | 111 008 01 | 254 x 180 x 90 |
| PS 2518 -11-t | 116 508 01 | PS 2518 -11-tm | 106 508 01 | PS 2518 -11-to | 111 508 01 | 254 x 180 x 111 |
| PS 2518 -16-t | 117 008 01 | PS 2518 -16-tm | 107 008 01 | PS 2518 -16-to | 112 008 01 | 254 x 180 x 165 |
| PS 2518 -21-t | 117 508 01 | PS 2518 -21-tm | 107 508 01 | PS 2518 -21-to | 112 508 01 | 254 x 180 x 215 |
| PS 3625 -11-t | 116 012 01 | PS 3625 -11-tm | 106 012 01 | PS 3625 -11-to | 111 012 01 | 360 x 254 x 111 |
| PS 3625 -16-t | 116 512 01 | PS 3625 -16-tm | 106 512 01 | PS 3625 -16-to | 111 512 01 | 360 x 254 x 165 |
| PS 3625 -21-t | 117 012 01 | PS 3625 -21-tm | 107 012 01 | PS 3625 -21-to | 112 012 01 | 360 x 254 x 215 |

TK Polycarbonate

- glass-fibre reinforced
- flame-resistant
- UV-resistant
- temperature-resistant to 120°C



| Base grey lid grey | | | | | | | |
|-------------------------------------|------------|--|---------------------------------|------------|-----------------------|------------|-----------------|
| with Pg knockouts | | | with metric knockouts | | with smooth walls* | | |
| Type | Order N° | | Type | Order N° | Type | Order N° | Dimensions |
| PC 77 - 6 | 125 401 01 | | PC 77 - 6-m | 127 401 01 | PC 77 - 6-o | 120 401 01 | 65 x 65 x 57 |
| PC 77 - 8 | 125 901 01 | | PC 77 - 8-m | 127 901 01 | PC 77 - 8-o | 120 901 01 | 65 x 65 x 81 |
| PC 97 - 6 | 125 402 01 | | PC 97 - 6-m | 127 402 01 | PC 97 - 6-o | 120 402 01 | 94 x 65 x 57 |
| PC 97 - 8 | 125 902 01 | | PC 97 - 8-m | 127 902 01 | PC 97 - 8-o | 120 902 01 | 94 x 65 x 81 |
| PC 99 - 6 | 125 403 01 | | PC 99 - 6-m | 127 403 01 | PC 99 - 6-o | 120 403 01 | 94 x 94 x 57 |
| PC 99 - 8 | 125 903 01 | | PC 99 - 8-m | 127 903 01 | PC 99 - 8-o | 120 903 01 | 94 x 94 x 81 |
| PC 1111 - 7 | 125 404 01 | | PC 1111 - 7-m | 127 404 01 | PC 1111 - 7-o | 120 404 01 | 110x 110 x 66 |
| PC 1111 - 9 | 125 904 01 | | PC 1111 - 9-m | 127 904 01 | PC 1111 - 9-o | 120 904 01 | 110x 110 x 90 |
| PC 1309 - 6 | 125 409 01 | | PC 1309 - 6-m | 127 409 01 | PC 1309 - 6-o | 120 409 01 | 130 x 94 x 57 |
| PC 1309 - 8 | 125 909 01 | | PC 1309 - 8-m | 127 909 01 | PC 1309 - 8-o | 120 909 01 | 130 x 94 x 81 |
| PC 1313 - 7 | 125 405 01 | | PC 1313 - 7-m | 127 405 01 | PC 1313 - 7-o | 120 405 01 | 130 x 130 x 75 |
| PC 1313 -10 | 125 905 01 | | PC 1313 -10-m | 127 905 01 | PC 1313 -10-o | 120 905 01 | 130 x 130 x 99 |
| PC 1809 - 6 | 125 410 01 | | PC 1809 - 6-m | 127 410 01 | PC 1809 - 6-o | 120 410 01 | 180 x 94 x 57 |
| PC 1809 - 8 | 125 910 01 | | PC 1809 - 8-m | 127 910 01 | PC 1809 - 8-o | 120 910 01 | 180 x 94 x 81 |
| PC 1811 - 9 | 125 406 01 | | PC 1811 - 9-m | 127 406 01 | PC 1811 - 9-o | 120 406 01 | 180 x 110 x 90 |
| PC 1811 -11 | 125 906 01 | | PC 1811 -11-m | 127 906 01 | PC 1811 -11-o | 120 906 01 | 180 x 110 x 111 |
| PC 1811 -16 | 126 406 01 | | PC 1811 -16-m | 128 406 01 | PC 1811 -16-o | 121 406 01 | 180 x 110 x 165 |
| PC 1818 - 9 | 125 407 01 | | PC 1818 - 9-m | 127 407 01 | PC 1818 - 9-o | 120 407 01 | 182 x 180 x 90 |
| PC 1818 -11 | 125 907 01 | | PC 1818 -11-m | 127 907 01 | PC 1818 -11-o | 120 907 01 | 182 x 180 x 111 |
| PC 1818 -16 | 126 407 01 | | PC 1818 -16-m | 128 407 01 | PC 1818 -16-o | 121 407 01 | 182 x 180 x 165 |
| PC 1818 -21 | 126 907 01 | | PC 1818 -21-m | 128 907 01 | PC 1818 -21-o | 121 907 01 | 182 x 180 x 215 |
| PC 2518 - 9 | 125 408 01 | | PC 2518 - 9-m | 127 408 01 | PC 2518 - 9-o | 120 408 01 | 254 x 180 x 90 |
| PC 2518 -11 | 125 908 01 | | PC 2518 -11-m | 127 908 01 | PC 2518 -11-o | 120 908 01 | 254 x 180 x 111 |
| PC 2518 -16 | 126 408 01 | | PC 2518 -16-m | 128 408 01 | PC 2518 -16-o | 121 408 01 | 254 x 180 x 165 |
| PC 2518 -21 | 126 908 01 | | PC 2518 -21-m | 128 908 01 | PC 2518 -21-o | 121 908 01 | 254 x 180 x 215 |
| PC 3625 -11 | 125 412 01 | | PC 3625 -11-m | 127 412 01 | PC 3625 -11-o | 120 412 01 | 360 x 254 x 111 |
| PC 3625 -16 | 125 912 01 | | PC 3625 -16-m | 127 912 01 | PC 3625 -16-o | 120 912 01 | 360 x 254 x 165 |
| PC 3625 -21 | 126 412 01 | | PC 3625 -21-m | 128 412 01 | PC 3625 -21-o | 121 412 01 | 360 x 254 x 215 |

* only available in UK



| Base grey lid transparent | | | | | | |
|--|------------|---------------------------------|------------|-----------------------|------------|-----------------|
| with Pg knockouts | | with metric knockouts | | with smooth walls* | | |
| Type | Order N° | Type | Order N° | Type | Order N° | Dimensions |
| PC 77- 6 -t | 135 001 01 | PC 77- 6 -tm | 137 001 01 | PC 77- 6 -to | 130 001 01 | 65 x 65 x 57 |
| PC 77- 8 -t | 135 501 01 | PC 77- 8 -tm | 137 501 01 | PC 77- 8 -to | 130 501 01 | 65 x 65 x 81 |
| PC 97- 6 -t | 135 002 01 | PC 97- 6 -tm | 137 002 01 | PC 97- 6 -to | 130 002 01 | 94 x 65 x 57 |
| PC 97- 8 -t | 135 502 01 | PC 97- 8 -tm | 137 502 01 | PC 97- 8 -to | 130 502 01 | 94 x 65 x 81 |
| PC 99- 6 -t | 135 003 01 | PC 99- 6 -tm | 137 003 01 | PC 99- 6 -to | 130 003 01 | 94 x 94 x 57 |
| PC 99- 8 -t | 135 503 01 | PC 99- 8 -tm | 137 503 01 | PC 99- 8 -to | 130 503 01 | 94 x 94 x 81 |
| PC 1111 - 7 -t | 135 004 01 | PC 1111 - 7 -tm | 137 004 01 | PC 1111 - 7 -to | 130 004 01 | 110x 110 x 66 |
| PC 1111 - 9 -t | 135 504 01 | PC 1111 - 9 -tm | 137 504 01 | PC 1111 - 9 -to | 130 504 01 | 110x 110 x 90 |
| PC 1309 - 6 -t | 135 009 01 | PC 1309 - 6 -tm | 137 009 01 | PC 1309 - 6 -to | 130 009 01 | 130 x 94 x 57 |
| PC 1309 - 8 -t | 135 509 01 | PC 1309 - 8 -tm | 137 509 01 | PC 1309 - 8 -to | 130 509 01 | 130 x 94 x 81 |
| PC 1313 - 7 -t | 135 005 01 | PC 1313 - 7 -tm | 137 005 01 | PC 1313 - 7 -to | 130 005 01 | 130 x 130 x 75 |
| PC 1313 -10 -t | 135 505 01 | PC 1313 -10 -tm | 137 505 01 | PC 1313 -10 -to | 130 505 01 | 130 x 130 x 99 |
| PC 1809 - 6 -t | 135 010 01 | PC 1809 - 6 -tm | 137 010 01 | PC 1809 - 6 -to | 130 010 01 | 180 x 94 x 57 |
| PC 1809 - 8 -t | 135 510 01 | PC 1809 - 8 -tm | 135 510 01 | PC 1809 - 8 -to | 130 510 01 | 180 x 94 x 81 |
| PC 1811 - 9 -t | 135 006 01 | PC 1811 - 9 -tm | 137 006 01 | PC 1811 - 9 -to | 130 006 01 | 180 x 110 x 90 |
| PC 1811 -11 -t | 135 506 01 | PC 1811 -11 -tm | 137 506 01 | PC 1811 -11 -to | 130 506 01 | 180 x 110 x 111 |
| PC 1811 -16 -t | 136 006 01 | PC 1811 -16 -tm | 138 006 01 | PC 1811 -16 -to | 131 006 01 | 180 x 110 x 165 |
| PC 1818 - 9 -t | 135 007 01 | PC 1818 - 9 -tm | 137 007 01 | PC 1818 - 9 -to | 130 007 01 | 182 x 180 x 90 |
| PC 1818 -11 -t | 135 507 01 | PC 1818 -11 -tm | 137 507 01 | PC 1818 -11 -to | 130 507 01 | 182 x 180 x 111 |
| PC 1818 -16 -t | 136 007 01 | PC 1818 -16 -tm | 138 007 01 | PC 1818 -16 -to | 131 007 01 | 182 x 180 x 165 |
| PC 1818 -21 -t | 136 507 01 | PC 1818 -21 -tm | 138 507 01 | PC 1818 -21 -to | 131 507 01 | 182 x 180 x 215 |
| PC 2518 - 9 -t | 135 008 01 | PC 2518 - 9 -tm | 137 008 01 | PC 2518 - 9 -to | 130 008 01 | 254 x 180 x 90 |
| PC 2518 -11 -t | 135 508 01 | PC 2518 -11 -tm | 137 508 01 | PC 2518 -11 -to | 130 508 01 | 254 x 180 x 111 |
| PC 2518 -16 -t | 136 008 01 | PC 2518 -16 -tm | 138 008 01 | PC 2518 -16 -to | 131 008 01 | 254 x 180 x 165 |
| PC 2518 -21 -t | 136 508 01 | PC 2518 -21 -tm | 138 508 01 | PC 2518 -21 -to | 131 508 01 | 254 x 180 x 215 |
| PC 3625 -11 -t | 135 012 01 | PC 3625 -11 -tm | 137 012 01 | PC 3625 -11 -to | 130 012 01 | 360 x 254 x 111 |
| PC 3625 -16 -t | 135 512 01 | PC 3625 -16 -tm | 137 512 01 | PC 3625 -16 -to | 130 512 01 | 360 x 254 x 165 |
| PC 3625 -21 -t | 136 012 01 | PC 3625 -21 -tm | 138 012 01 | PC 3625 -21 -to | 131 012 01 | 360 x 254 x 215 |

* only available in UK

TK Polycarbonate

with  Certification

- glass-fibre reinforced
- flame-resistant
- UV-resistant
- temperature-resistant to 120°C



| Base grey lid grey | | | | Base grey lid transparent | | | | |
|-------------------------------------|------------|---------------------------------|------------|--|------------|---------------------------------|------------|-----------------|
| with Pg knockouts | | with metric knockouts | | with Pg knockouts | | with metric knockouts | | |
| Type | Order N° | Type | Order N° | Type | Order N° | Type | Order N° | Dimensions |
| PC 77- 6 | 125 401 52 | PC 77- 6-m | 127 401 52 | PC 77- 6-t | 135 001 52 | PC 77- 6-tm | 137 001 52 | 65 x 65 x 57 |
| PC 77- 8 | 125 901 52 | PC 77- 8-m | 127 901 52 | PC 77- 8-t | 135 501 52 | PC 77- 8-tm | 137 501 52 | 65 x 65 x 81 |
| PC 97- 6 | 125 402 52 | PC 97- 6-m | 127 402 52 | PC 97- 6-t | 135 002 52 | PC 97- 6-tm | 137 002 52 | 94 x 65 x 57 |
| PC 97- 8 | 125 902 52 | PC 97- 8-m | 127 902 52 | PC 97- 8-t | 135 502 52 | PC 97- 8-tm | 137 502 52 | 94 x 65 x 81 |
| PC 99- 6 | 125 403 52 | PC 99- 6-m | 127 403 52 | PC 99- 6-t | 135 003 52 | PC 99- 6-tm | 137 003 52 | 94 x 94 x 57 |
| PC 99- 8 | 125 903 52 | PC 99- 8-m | 127 903 52 | PC 99- 8-t | 135 503 52 | PC 99- 8-tm | 137 503 52 | 94 x 94 x 81 |
| PC 1111 - 7 | 125 404 52 | PC 1111 - 7-m | 127 404 52 | PC 1111 - 7-t | 135 004 52 | PC 1111 - 7-tm | 137 004 52 | 110x 110 x 66 |
| PC 1111 - 9 | 125 904 52 | PC 1111 - 9-m | 127 904 52 | PC 1111 - 9-t | 135 504 52 | PC 1111 - 9-tm | 137 504 52 | 110x 110 x 90 |
| PC 1309 - 6 | 125 409 52 | PC 1309 - 6-m | 127 409 52 | PC 1309 - 6-t | 135 009 52 | PC 1309 - 6-tm | 137 009 52 | 130 x 94 x 57 |
| PC 1309 - 8 | 125 909 52 | PC 1309 - 8-m | 127 909 52 | PC 1309 - 8-t | 135 509 52 | PC 1309 - 8-tm | 137 509 52 | 130 x 94 x 81 |
| PC 1313 - 7 | 125 405 52 | PC 1313 - 7-m | 127 405 52 | PC 1313 - 7-t | 135 005 52 | PC 1313 - 7-tm | 137 005 52 | 130 x 130 x 75 |
| PC 1313 -10 | 125 905 52 | PC 1313 -10-m | 127 905 52 | PC 1313 -10-t | 135 505 52 | PC 1313 -10-tm | 137 505 52 | 130 x 130 x 99 |
| PC 1809 - 6 | 125 410 52 | PC 1809 - 6-m | 127 410 52 | PC 1809 - 6-t | 135 010 52 | PC 1809 - 6-tm | 137 010 52 | 180 x 94 x 57 |
| PC 1809 - 8 | 125 910 52 | PC 1809 - 8-m | 127 910 52 | PC 1809 - 8-t | 135 510 52 | PC 1809 - 8-tm | 137 510 52 | 180 x 94 x 81 |
| PC 1811 - 9 | 125 406 52 | PC 1811 - 9-m | 127 406 52 | PC 1811 - 9-t | 135 006 52 | PC 1811 - 9-tm | 137 006 52 | 180 x 110 x 90 |
| PC 1811 -11 | 125 906 52 | PC 1811 -11-m | 127 906 52 | PC 1811 -11-t | 135 506 52 | PC 1811 -11-tm | 137 506 52 | 180 x 110 x 111 |
| PC 1811 -16 | 126 406 52 | PC 1811 -16-m | 128 406 52 | PC 1811 -16-t | 136 006 52 | PC 1811 -16-tm | 138 006 52 | 180 x 110 x 165 |
| PC 1818 - 9 | 125 407 52 | PC 1818 - 9-m | 127 407 52 | PC 1818 - 9-t | 135 007 52 | PC 1818 - 9-tm | 137 007 52 | 182 x 180 x 90 |
| PC 1818 -11 | 125 907 52 | PC 1818 -11-m | 127 907 52 | PC 1818 -11-t | 135 507 52 | PC 1818 -11-tm | 137 507 52 | 182 x 180 x 111 |
| PC 1818 -16 | 126 407 52 | PC 1818 -16-m | 128 407 52 | PC 1818 -16-t | 136 007 52 | PC 1818 -16-tm | 138 007 52 | 182 x 180 x 165 |
| PC 1818 -21 | 126 907 52 | PC 1818 -21-m | 128 907 52 | PC 1818 -21-t | 136 507 52 | PC 1818 -21-tm | 138 507 52 | 182 x 180 x 215 |
| PC 2518 - 9 | 125 408 52 | PC 2518 - 9-m | 127 408 52 | PC 2518 - 9-t | 135 008 52 | PC 2518 - 9-tm | 137 008 52 | 254 x 180 x 90 |
| PC 2518 -11 | 125 908 52 | PC 2518 -11-m | 127 908 52 | PC 2518 -11-t | 135 508 52 | PC 2518 -11-tm | 137 508 52 | 254 x 180 x 111 |
| PC 2518 -16 | 126 408 52 | PC 2518 -16-m | 128 408 52 | PC 2518 -16-t | 136 008 52 | PC 2518 -16-tm | 138 008 52 | 254 x 180 x 165 |
| PC 2518 -21 | 126 908 52 | PC 2518 -21-m | 128 908 52 | PC 2518 -21-t | 136 508 52 | PC 2518 -21-tm | 138 508 52 | 254 x 180 x 215 |
| PC 3625 -11 | 125 412 52 | PC 3625 -11-m | 127 412 52 | PC 3625 -11-t | 135 012 52 | PC 3625 -11-tm | 137 012 52 | 360 x 254 x 111 |
| PC 3625 -16 | 125 912 52 | PC 3625 -16-m | 127 912 52 | PC 3625 -16-t | 135 512 52 | PC 3625 -16-tm | 137 512 52 | 360 x 254 x 165 |
| PC 3625 -21 | 126 412 52 | PC 3625 -21-m | 128 412 52 | PC 3625 -21-t | 136 012 52 | PC 3625 -21-tm | 138 012 52 | 360 x 254 x 215 |