



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1530 Shields Drive  
Waukegan, IL 60085  
Toll-Free (800) 323-9355  
Fax: (847) 689-1192

**PART NUMBER:** 20137  
**DESCRIPTION:** 14/3 STRANDED SJTOW FLEXIBLE POWER CABLE  
**CONSTRUCTION:** This cable consists of three bare copper insulated conductors cabled with fillers with an overall jacket.  
**APPROVALS:** Underwriter's Laboratory, Canadian Standards Association, NEC Article 400  
**APPLICATION:** 300 Volt Outdoor and Oil Portable Power Cable Applications

---

### Construction Parameters:

Conductor	14 AWG Bare Copper
Stranding	41/30
Insulation Material	PVC
Insulation Thickness	0.031" Nom.
Insulated Conductor Diameter	0.136" Nom.
Number of Conductors	3
Lay Length	2.75" Nom.
Lay Direction	All Layers Left Hand Lay
Filler	Polypropylene
Separator	Paper Tissue
Jacket Material	PVC
Jacket Thickness	0.036" Nom.
Overall Cable Diameter	0.365" Nom.
Approximate Cable Weight	79.6 Lbs/1M' Nom.
Flame Rating	UL/CSA Horizontal Flame Test

---

### Electrical Properties:

Temperature Rating	-20°C to 60°C
Operating Voltage	300 V RMS Max.
DC Resistance per Conductor @ 20°C	2.53 Ohms/1M' Nom.

---

Insulation Colors	Black White Green
Jacket Color	Gray or Yellow (Other colors available for minimum order)

Legend (Indent Print)	<b>CCI ROYAL</b> 14 AWG (2.08mm <sup>2</sup> ) 3/C SJTOW E54864 (UL) 60C 300V -- CSA LL39753 SJTOW 60C 300V FT1 WATER-RESISTANT
-----------------------	---

*This product complies with European Directive 2002/95/EC (RoHS)*  
On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name \_\_\_\_\_

Customer Approval \_\_\_\_\_

Specification Issue Date: September 21, 2005