



Sample photo

Order symbol: PC C 85 T
Product nbr: 8724006
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074002044
EI. number:
 Finland 3423507
 Denmark 8212001543
 Italy 7202025
 Sweden 2536841

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:			L		W		H		Rating:	
mm:	140	80	85					Ingress Protection (EN 60529): IP 66/67		
inch:	5.5	3.1	3.3					Impact Resistance (EN 50102): IK 08		
Materials:										
Material:	PC									
Base colour:	RAL 7035									
Cover colour:	Clear transparent									
Cover screws material:	Polyamide									
Cover screws colour:	Grey									
Gasket material:	Polyurethane									
Temperatures:										
Short term:	-40 ... 120 °C									
Continuous:	-40 ... 80 °C									
Short term:	-40 ... 250 °F									
Continuous:	-40 ... 175 °F									
Accessories:										
C-MP	Mounting plate									
CHM-3	DIN-35 Mounting rail									
FP 22040	Mounting foot kit (2 pcs)									
Certificates:										
Germanischer Lloyd (GL)										
Underwriters Laboratories										
Canadian Standards Association										
Fimko										
Europe EN 50298 1998										
UL Canada										
Gost R										
Electrical insulation: Totally insulated										
Halogen free (DIN/VDE 0472, Part 815): Yes										
UV resistance: UL 508										
Flammability Rating (UL 746 C 5): UL 94 5V										
Glow Wire Test (IEC 695-2-1) °C: 960										
NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13										

