

00 20

00 20 Tool Box, 4 parts
with VDE tools



00 20 15

- ▶ all pliers VDE tested according DIN/IEC 60900 ⚡ 1000 V ⚠
- ▶ high quality, versatile, shock-resistant plastic case (Model 00 21 15 LE)
- ▶ foam insert with honeycomb structure for variable equipment
- ▶ other assortment on request

| Article-No. | EAN-Code | Contents Article | g |
|-------------|----------|----------------------|-------|
| | 4003773- | | |
| 00 20 15 | 024804 | 03 06 180 ⚡ 1000 V ⚠ | 1,500 |
| | | 11 06 160 ⚡ 1000 V ⚠ | |
| | | 26 16 200 ⚡ 1000 V ⚠ | |
| | | 70 06 160 ⚡ 1000 V ⚠ | |

00 21

00 21 Tool Box, 7 parts
for electrical contractors



00 21 15

- ▶ all pliers except Water Pump Pliers VDE tested according DIN/IEC 60900 ⚡ 1000 V
- ▶ high quality, versatile, shock-resistant plastic case (Model 00 21 15 LE)
- ▶ foam insert with honeycomb structure for variable equipment
- ▶ other assortment on request

Model 00 21 15 LE:

- ▶ without tools
- ▶ external dimensions (WxHxD): 327x65x275 mm

| Article-No. | EAN-Code | Contents Article | g |
|-------------|----------|---------------------------|-------|
| | 4003773- | | |
| 00 21 15 | 042853 | 03 06 180 ⚡ 1000 V ⚠ | 1,500 |
| | | 26 16 200 ⚡ 1000 V ⚠ | |
| | | 70 06 160 ⚡ 1000 V ⚠ | |
| | | 88 03 180 | |
| | | WERA 0.4 x 2.5 ⚡ 1000 V ⚠ | |
| | | WERA 0.8 x 4.0 ⚡ 1000 V ⚠ | |
| | | WERA PH1 ⚡ 1000 V ⚠ | |
| 00 21 15 LE | | empty | 532 |