






13 12 11 10 9 8 7 6 5 4 3 2 1

J  
I  
H  
G  
F  
E  
D  
C  
B  
A

J  
I  
H  
G  
F  
E  
D  
C  
B  
A



RECEPTACLE

3	I
2	I
1	I
SHT.	REV.

UPDATE REVISIONS	
EC NO. UCP2007-2085	2007/04/13
DRWN:PRD DER	2007/04/16
CHKD: AEL/HAG	2007/04/16
APPR: FSM/TH	2007/04/19
REV	DESCRIPTION

QUALITY SYMBOLS	▽=0
	▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± .007	± .0007
3 PLACES	± .010	± .0010
2 PLACES	± 0.18	± .010
1 PLACE	± 0.25	± .010
ANGULAR ± 1 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
IN/MM	
DRAWN BY	DATE
GEP	1988/09/21
CHECKED BY	DATE
RW	1988/09/21
APPROVED BY	DATE
RAS	1988/09/21
MATERIAL NO.	
SEE CHART	

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
2:1	INCH	☑
TITLE		
.125/(3.17) HOUSING, PLUG AND RECEPTACLE		
4 CKT .330/(8.38) CTRS.		
DOCUMENT NO.		SHEET NO.
SD-42179-4*		1 OF 3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

12 11 10 9 8 7 6 5 4 3 2 1

	13	12	11	10	9
	PLUG			RECEPTACLE	
J	PART NO.	ENG. NO.		PART NO.	ENG. NO.
	03-12-2046	42179-4P1		03-12-1046	42179-4
	03-12-2045	42179-4P		03-12-6040	42179-4
	03-12-7042	42179-4PYW		03-12-6041	42179-4
	03-12-7043	42179-4PIYW			
	03-12-7040	42179-4PBK			
I	03-12-7041	42179-4PIBK			
	03-12-7044	42179-4PIRD	OBSOLETE		
	03-12-7045	42179-4P2			

**LEGEND:**

42179-4\*\*\*

SIZE: \_\_\_\_\_

MOUNTING TYPE: \_\_\_\_\_



P = PLUG  
R = RECEPTACLE

FEATURE OPTIONS: \_\_\_\_\_

BLANK = WITH MOUNTING EARS (PLUG ONLY)  
1 = WITHOUT MOUNTING EARS  
2 = WITH MOUNTING EARS (PLUG ONLY); WITHOUT LOCKING RAMP

COLOR: \_\_\_\_\_

BLANK = 94V-2; TRANSLUCENT NATURAL COLOR  
AM=AMBER BK=BLACK BU=BLUE  
BN=BROWN GY=GRAY GN=GREEN  
OR=ORANGE RD=RED YW=YELLOW



NOTES:

