



No. of contacts	Y	Press-fit technology	
		Termination length	
max. 54	1-row		
		2.8	981-nn010-b1
		5.6	981-nn011-b1
		7.8	981-nn012-b1
max. 108	2-row	10.6	981-nn013-b1
		2.8	982-nn010-b1
		5.6	982-nn011-b1

**Accessories**

- Press-fit tool (see page 214)
- Support tool (see page 215)

**Note**

Surfaces Y side (b):  
 b = 2: 0.80  $\mu$ m Au on 1.27  $\mu$ m Ni  
 b = 3: 0.15  $\mu$ m Au on 1.27  $\mu$ m Ni

**Ordering note**

nn = no. of contacts/row  
 b = surface Y side

