

Steel industrial boxes

Selection guide

Universal security application				
				
IP 66	IP 66	IP 66	IP 66	IP 55
Page 1/4			Page 1/6	Page 1/8

External dimensions (mm)			Steel industrial box references			IK 10	Opaque door + screws
Height	Width	Depth	IK 08				
			Empty	Plate	Uprights (1)		
80	80	45	NSYSBS884	-	-	-	-
100	100	55	NSYSBS10105	-	-	-	-
130	130	60	NSYSBS13136	-	-	-	-
160	160	65	NSYSBS16166	-	-	-	-
165	120	65	NSYSBS16126	NSYSBS16126S	-	-	-
180	130	96		-	-	-	NSYSBS18139F
180	165	96		-	-	-	NSYSBS18169F
200	200	90	NSYSBS20209	NSYSBS20209S	-	-	-
230	210	126		-	-	-	NSYSBS232112F
250	250	100	NSYSBS252510	NSYSBS252510S	-	-	-
300	200	110		-	NSYSBS302011R	-	-
300	200	150		-	-	NSYSBS302015	-
300	300	100	NSYSBS303010	NSYSBS303010S	-	-	-
300	300	150		-	-	NSYSBS303015	-
400	200	110		-	NSYSBS402011R	-	-
400	300	150		-	-	NSYSBS403015	-
400	400	110	NSYSBS404011	NSYSBS404011S	-	-	-
500	200	110		-	NSYSBS502011R	-	-
500	300	110		-	NSYSBS503011R	-	-
500	300	200		-	-	NSYSBS503020	-
600	200	110		-	NSYSBS602011R	-	-
600	300	110		-	NSYSBS603011R	-	-

(1) Uprights along small sides (Width)



Specific

Our specific offer: special dimensions and cut-outs. Please contact us.