

AZURO Wireless Optical Mobile Mouse

M-305



Facts & Features

- Wireless freedom with 2.4 GHz wireless technology offering a 10 m range and interruption-free transmission
- Optical sensor* with adjustable resolution (slow / quick) via easy-to-reach switches on the top side of the mouse
- On/Off switch – saves the battery when not in use and while on the move
- Plug & Play for easy start up with no software installation

*Optimal functioning on non-reflective surfaces only

Delivery volume

- 1 AZURO mouse
- 1 USB receiver
- 1 printed manual
- 1 battery (AA)

Approvals

- CE, FCC

Operating system

- Microsoft Windows™ 2000, XP, Vista

System requirements

- USB interface

Technical data

- Number of buttons:
5 buttons
- Weight:
approx. 100g (Mouse)
approx. 10g (Receiver)
approx. 160g (with Packaging)
- Dimensions in mm:
approx. 105 x 65 x 40 (Mouse)
approx. 156 x 230 x 45 (Packaging)
- Storage temperature:
-20°C to 65°C
- Operating temperature:
0°C to 50°C
- Transmission range:
approx. 10m
- Resolution:
500 dpi / 1000 dpi
- Frequency range:
2,4 GHz
- Interface:
USB
- Current consumption:
typ. 30 mA (Receiver)
max. 25 mA (Mouse)
- Packaging unit:
20 mice per master carton
16 master cartons per pallet

Order description

<i>Order number</i>	<i>Housing colour</i>	<i>Interface</i>	<i>EAN-Code</i>
M-305	blue/black	USB	4025112071072

Cherry GmbH
Cherrystraße
91275 Auerbach/Opf.
Germany

Phone: +49 9643 18-0
Internet: www.cherry.de
www.cherrycorp.com

Sales: +49 1805 243779 (01805-Cherry)
E-Mail: sales@cherry.de
Fax: +49 9643 18-1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 Cherry GmbH, Last update: 18.07.2008_V01

