

Metal Oxide Resistors

CCR-03

(2 Flap FL24/10) 48 Values / 810 Pieces
Miniature Power Resistors

Type/Brand: RNS-RSS1 / FUKUSHIMA FUTABA

Size: 0309 (2,8øx 9,5mm)

Wattage: 1,0W

Tolerance: ±5%

Values: 0,22Ohm-47KOhm (E6/E12)

TC: 350 ppm/°C

Values-Quantities Selection:

0,22	20x	0,33	20x	0,47	20x	0,68	20x	1	20x	1,5	20x
2,2	20x	3,3	20x	4,7	20x	6,8	20x	10	20x	15	20x
22	20x	33	20x	47	20x	68	20x	100	20x	150	20x
180	10x	220	20x	270	10x	330	20x	390	10x	470	20x
560	10x	680	20x	820	10x	1K0	20x	1K2	10x	1K5	20x
1K8	10x	2K2	20x	2K7	10x	3K3	20x	3K9	10x	4K7	20x
5K6	10x	6K8	20x	8K2	10x	10K	20x	12K	10x	15K	20x
18K	10x	22K	20x	27K	10x	33K	20x	39K	10x	47K	20x