

Power Resistors

CCR-31

(1 Flap FL16/20) 14 Values / 195 Pieces
Low Ohm Metalband Resistors

Type/Brand: MPC 70-76-702 / FUKUSHIMA FUTABA
Style: Rectangular Ceramic case with radial leads
Values: 0,01Ω-1,0Ω (E6/E12)
Temperature: -55 at + 200°C
Wattage: 2W
Tolerance: ±10%
TK: +/- 350ppm/°C

Values-Quantities-Selection:

0,01Ω	20x	0,15Ω	15x	0,33Ω	15x	0,56Ω	10x	1,00Ω	15x
0,05Ω	20x	0,22Ω	15x	0,39Ω	10x	0,68Ω	15x	2x0,47Ω	10x
0,10Ω	15x	0,27Ω	10x	0,47Ω	15x	0,82Ω	10x		

CCR-32

(1 Flap FL16/20) 15 Values / 195 Pieces
Low Ohm Metalband Resistors

Type/Brand: MPC 71-75-722 / FUKUSHIMA FUTABA
Style: Rectangular Ceramic case with radial leads
Values: 0,01Ω-2,2Ω (E6/E12)
Temperature: -55 at +200°C
Wattage: 5W
Tolerance: ±10%
TK: +/- 350ppm/°C

Values-Quantities-Selection:

0,01Ω	15x	0,15Ω	15x	0,33Ω	15x	0,56Ω	10x	1,00Ω	15x
0,05Ω	15x	0,22Ω	15x	0,39Ω	10x	0,68Ω	15x	2,20Ω	10x
0,10Ω	15x	0,27Ω	10x	0,47Ω	15x	0,82Ω	10x	2x0,47Ω	10x

CCR-33

(1 Flap FL16/20) 16 Values / 240 Pieces
Power Resistors with wire- or metaloxide element

Type/Brand: CWR-COR / FUKUSHIMA FUTABA

Style: Rectangular Ceramic case with radial leads

Values: 1,5Ω-1,0KΩ (E6)

Wattage: 2W

Tolerance: ±5%

TK: 350ppm/°C

Values-Quantities-Selection:

1,5Ω	15x	6,8Ω	15x	33Ω	15x	220Ω	15x
2,2Ω	15x	10Ω	15x	47Ω	15x	330Ω	15x
3,3Ω	15x	15Ω	15x	68Ω	15x	470Ω	15x
4,7Ω	15x	22Ω	15x	100Ω	15x	1,0KΩ	15x

CCR-34

(1 Flap FL16/20) 16 Values / 160 Pieces
Power Resistors with wire- or metaloxide element

Type/Brand: CWR-COR/FUKUSHIMA FUTABA

Style: Rectangular Ceramic case with radial leads

Values : 1,5Ω-1,0KΩ (E6)

Wattage: 5W

Tolerance: ±5%

TK: 350ppm/°C

Values-Quantities-Selection:

1,5Ω	10x	6,8Ω	10x	33Ω	10x	220Ω	10x
2,2Ω	10x	10Ω	10x	47Ω	10x	330Ω	10x
3,3Ω	10x	15Ω	10x	68Ω	10x	470Ω	10x
4,7Ω	10x	22Ω	10x	100Ω	10x	1,0KΩ	10x