

# TECHNICAL DATA

**Model Number:** MB120A050U/D**Type** Multi--Voltage AC/AC Adaptor**Electrical Data**

<b>Input</b>	Input Voltage/Frequency	230V/50Hz
	Input Power	7.6W
<b>Output</b>	Rated Output Voltage	12V
	Rated Output Load Current	500mA
	Rated Output Power	6 VA
<b>Resistance</b>	Insulation Resistance	100MΩ(measured with 500V DC voltage)
<b>Protection</b>	Thermal Protection	Thermal fuse:125□/2A
	Withstand Voltage (Hi-Pot)	AC 3750V 50Hz for 1minute or AC4000V 2seconds

**Mechanical Data**

Supply Connection Type	SCHUKO type DIN49 MWST-1 464/F
Primary Turns & Wire Gauge	3220T/0.09mm
Secondary Turns & Wire Gauge	224T/0.38mm
Core Size	41mm×16mm
Output Plug Dimensions	5.5×2.1 ×12mm
Polarity	
Unit Weight	242g
Dimensions	59(L)×50(W)×80(H)