

# Double Row Terminal Blocks

## Kulka® 605 GP Series

### 600 Volts

#### Specifications:

- Base, General Purpose Phenolic, 150°C
- JJ (GDI-30F) Material Available
- Open Back Design (Insulator Strip Required for Voltage Rating)
- Screws, #1/4-28 Binder Head, Slotted, Brass
- Terminals, Plated Brass
- 1-6 Poles
- 1-1/8" Centers
- Wire Range With Wire Binding Screw #2-#12 AWG – 90 Amps
- The Suitability Of These Devices For Greater Currents Shall Be Determined In The End-Use Application
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- CE

Catalog #	# of poles	Dimensions	
		A	B
605 GP 01 PSB	1	2.88	2.25
605 GP 02 PSB	2	4.00	3.38
605 GP 03 PSB	3	5.13	4.50
605 GP 04 PSB	4	6.25	5.63
605 GP 05 PSB	5	7.38	6.75
605 GP 06 PSB	6	8.50	7.88

MM = Dim X 25.4

