

Data Sheet Model No.: GP15AU

NO MERCURY ADDED

Description : Mercury & Cadmium Free Alkaline

Manganese Battery, AA Size

Chemical System : Alkaline Manganese

Nominal Voltage : 1.5 Volts

Nominal Dimensions: Ø14.5 mm x 50.5 mm

Terminals : Protruded positive(+) and flat negative(-)

contacts

Jacket : Foil jacket

Applications : All electronic devices, e.g. toys, digital

camera, mobile phone, PDA, photographic equipment, data banks, calculators, audio

appliances, remote controls, paging


machines.

Warranty Period : 36 months

Average Weight : 23g

Typical Service Life:

Discharge	Discharge	End Point	Service	
Resistance	Condition	Voltage	Life	
10 Ohms	24 Hrs/Day	0.9V	19.0Hrs	



At 20±2°C within 30 days of manufacture

Cross References:

GP	JIS	IEC	Eveready	Duracell
15AU	LR6	LR6	E91	MX1500

