

SKINDICHT® RWV SKINDICHT® RWV-M

Compact angle gland
with PG or metric connection thread



SKINDICHT® RWV 90° elbow


The locknut enables the angle gland to be secured in any position. The material is sea-water resistant, resistant to tropical conditions and to corrosion, when used in combination with grey cast iron or steel. The protection class depends on the special gland with which it is combined, but in the standard design is at least IP 55.

SKINDICHT® RWV without incised seal and compression screw


We also have SKINDICHT® RWV with O-ring and locknut.


Suitable accessories for metric thread see page 484.


Suitable accessories for PG thread see page 494.





Technical Data



 Material:
Body: Die cast zinc
Compression screw
and hexagonal nut:
Neopren
O-ring: Perbunan

 Protection class: IP 55

 Temperature range:
-20 °C to +80 °C
without incised seal
-20 °C to +100 °C

 Combination with other
cable glands possible

 Available also with metric
connection thread



Part number	Type	Holes in the intented sealing ring	Wrench size 1/2 mm	C mm	A mm	D mm	B mm	G mm	Pack size pieces
SKINDICHT® RWV									
5200 4180	RWV 7	5	15/13	26	20,5	8,5	15,3	14	25
5200 4190	RWV 9	5/8	18/15	28	23,5	9,5	18,3	17	25
5200 4200	RWV 11	7/10/12,5	21/18	31,5	26	10	21,9	20	25
5200 4210	RWV 13,5	7/10,5/13/16	23/20	34,5	28,5	10,5	24	22	25
5200 4220	RWV 16	8/10,5/13,5/16	26/22	35,5	31	11	26,1	24	10
5200 5420	RWV 21	11/15/18/20	32/28	42,5	33,5	11,5	32,5	30	10
5200 4225	RWV 29	19/23/27/31	41/37	59	43	13	42	40	10

Part number	Type	Holes in the intented sealing ring	Wrench size 1/2 mm	C mm	A mm	D mm	B mm	G mm	Pack size pieces
SKINDICHT® RWV without E+D									
5202 4020	RWV 7		15/13	26	20,5	8,5	15,3	14	25
5202 3970	RWV 9		18/15	28	23,5	9,5	18,3	17	25
5202 3980	RWV 11		21/18	31,5	26	10	21,9	20	25
5202 3990	RWV 13,5		23/20	34,5	28,5	10,5	24	22	25
5202 4000	RWV 16		26/22	35,5	31	11	26,1	24	10
5202 4010	RWV 21		32/28	42,5	33,5	11,5	32,5	30	10
5202 4015	RWV 29		41/37	59	43	13	42	40	10